



0 413 87

0 413 88









Technical characteristics see e-catalogue

Pack	Cat.Nos	
		electronic sirens For LED beacons Cat.Nos 0 413 86/87/88/92/93 and multi-sound electronic sirens Cat.No 0 413 98 (p. 394)
1	0 413 81	12/24 V ← and IP 65, side wiring, equipped with 2 cable glands Dimensions: height 46 mm, Ø92 mm
1	0 413 82	40/80 V and = IP 65, side wiring, equipped with 2 cable glands Dimensions: height 46 mm, Ø92 mm
1	0 413 83	120/240 V√ IP 65, side wiring, equipped with 2 cable glands Dimensions : height 46 mm, Ø92 mm
		Compact size LED beacons
		To be equipped with base Cat.No 0 413 81/82/83 Adjustable light intensity (3 levels) 5 separate light effects: steady, single or double flash, strobe effect, random Can be controlled via independent electrical contacts and/or push-buttons Dimensions: height 42.5 mm, Ø92 mm IP65 - IK 08 Power supply from 12 V and = to 230 V depending on the installed base
1	0 413 86	600 Candelas ● Orange
4	0.440.07	1100 Candelas

2500 Candelas
Green

Pack	Cat.Nos	Large size LED beacons
		To be equipped with base Cat.No 0 413 81/82/83 3 separate light effects: steady, rotating, flashing Can be controlled via independent electrical contacts Dimensions : height 110 mm, Ø92 mm IP65 - IK 08 Power supply from 12 V $\!\!\sim$ and $_{=}$ to 230 V $\!\!\sim$ depending on the installed base
		20 Candelas
1	0 413 92	Orange
1	0 413 93	13 Candelas Red
ī	0 413 93	₩ INEU