



Technical characteristics p. 254

Enclosures equipped with functional uprights and supplied with fixing supports for faceplates (fixing accessories for faceplates to be ordered separately p. 240)  
 Doors and side panels to be ordered separately  
 Take protection devices up to 630 A  
 Used to create assemblies certified IEC 61439-2  
 IP 40 with door  
 IP 30 without door  
 Removable, separable top and bottom panels  
 Can take Lina 25 ducting and IP 55 Cabstop cable gland plates (p. 241)

Pack	Cat.Nos	Enclosures				
<b>16 modules wide</b>						
Faceplates: RAL 9003						
Body: RAL 7016						
		Height (mm)		Width (mm)		Depth (mm)
		total	faceplate	total	usable	
1	3 375 21	824	750	454	350	249
1	3 375 31	974	900	454	350	249
1	3 375 41	1124	1050	454	350	249
1	3 375 51	1274	1200	454	350	249
1	3 375 61	1424	1350	454	350	249
1	3 375 71	1574	1500	454	350	249
1	3 375 81	1724	1650	454	350	249
1	3 375 91	1874	1800	454	350	249
1	3 376 01	2024	1950	454	350	249
1	3 376 11	2174	2100	454	350	249
1	3 376 21	2324	2250	454	350	249
<b>24 modules wide</b>						
1	3 375 22	824	750	604	574	249
1	3 375 32	974	900	604	574	249
1	3 375 42	1124	1050	604	574	249
1	3 375 52	1274	1200	604	574	249
1	3 375 62	1424	1350	604	574	249
1	3 375 72	1574	1500	604	574	249
1	3 375 82	1724	1650	604	574	249
1	3 375 92	1874	1800	604	574	249
1	3 376 02	2024	1950	604	574	249
1	3 376 12	2174	2100	604	574	249
1	3 376 22	2324	2250	604	574	249
<b>36 modules wide</b>						
1	3 375 23	824	750	804	774	249
1	3 375 33	974	900	804	774	249
1	3 375 43	1124	1050	804	774	249
1	3 375 53	1274	1200	804	774	249
1	3 375 63	1424	1350	804	774	249
1	3 375 73	1574	1500	804	774	249
1	3 375 83	1724	1650	804	774	249
1	3 375 93	1874	1800	804	774	249
1	3 376 03	2024	1950	804	774	249
1	3 376 13	2174	2100	804	774	249
1	3 376 23	2324	2250	804	774	249

Pack	Cat.Nos	Internal cable sleeves			
<b>Internal cable sleeve kits</b>					
For mounting on either the right or left inside XL <sup>3</sup> S 630 enclosures					
		Height (mm)			
		total	faceplate		
1	3 379 32	824	750		
1	3 379 33	974	900		
1	3 379 34	1124	1050		
1	3 379 35	1274	1200		
1	3 379 36	1424	1350		
1	3 379 37	1574	1500		
1	3 379 38	1724	1650		
1	3 379 39	1874	1800		
1	3 379 40	2024	1950		
1	3 379 41	2174	2100		
1	3 379 42	2324	2250		
<b>External cable sleeves</b>					
<b>Side cable sleeves</b>					
Fitted on either the right or left of enclosures using joining kits Cat.Nos 3 379 49/50					
		Height (mm)		Width (mm)	Depth (mm)
		total	faceplate	total	
1	3 375 20	824	750	324	249
1	3 375 30	974	900	324	249
1	3 375 40	1124	1050	324	249
1	3 375 50	1274	1200	324	249
1	3 375 60	1424	1350	324	249
1	3 375 70	1574	1500	324	249
1	3 375 80	1724	1650	324	249
1	3 375 90	1874	1800	324	249
1	3 376 00	2024	1950	324	249
1	3 376 10	2174	2100	324	249
1	3 376 20	2324	2250	324	249
<b>Side panels</b>					
Set of 2 panels					
For cabinets or cable sleeves with faceplate height (mm)					
1	3 378 62	750			
1	3 378 63	900			
1	3 378 64	1050			
1	3 378 65	1200			
1	3 378 66	1350			
1	3 378 67	1500			
1	3 378 68	1650			
1	3 378 69	1800			
1	3 378 70	1950			
1	3 378 71	2100			
1	3 378 72	2250			