

**XL<sup>3</sup> S 4000**

## selection chart

DEVICE	ENCLOSURE	POSITION	CONFIGURATION	FIXING DEVICES			FACEPLATES	
				RAIL	PLATE	BRACKETS	HEIGHT (MM)	
				FIXING ON RAIL			FIXING ON RAIL	
MCBS	16 modules wide	Vertical	-	3 382 20	-	-	150	3 382 51
	24 modules wide	Vertical	-	3 382 23	-	-	150	3 382 52
	36 modules wide	Vertical	-	3 382 26	-	-	150	3 382 53
DPX <sup>3</sup> 160	16 modules wide	Vertical	Without side motor-driven handle	3 382 20 + 4 210 71	-	-	300	3 382 71
		Vertical	With e.l.c.bs without side motor-driven handle	3 382 20 + 4 210 73	-	-	300	3 382 71
		Vertical	With side motor-driven handle	3 382 20 + 4 210 68	-	-	300	3 382 71
	24 modules wide	Vertical	Without side motor-driven handle	3 382 23 + 4 210 71	-	-	300	3 382 72
		Vertical	With e.l.c.bs without side motor-driven handle	3 382 23 + 4 210 73	-	-	300	3 382 72
		Vertical	With side motor-driven handle	3 382 23 + 4 210 68	-	-	300	3 382 72
	36 modules wide	Vertical	Without side motor-driven handle	3 382 26 + 4 210 71	-	-	300	3 382 73
		Vertical	With e.l.c.bs without side motor-driven handle	3 382 26 + 4 210 73	-	-	300	3 382 73
		Vertical	With side motor-driven handle	3 382 26 + 4 210 68	-	-	300	3 382 73
DPX <sup>3</sup> 250	16 modules wide	Vertical	Without side motor-driven handle	3 382 20 + 4 210 72	-	-	300	3 382 71
		Vertical	With e.l.c.bs without side motor-driven handle	3 382 20 + 4 210 74	-	-	300	3 382 71
		Vertical	With side motor-driven handle	3 382 20 + 4 210 69	-	-	300	3 382 71
	24 modules wide	Vertical	Without side motor-driven handle	3 382 23 + 4 210 72	-	-	400	3 382 81
		Vertical	With e.l.c.bs without side motor-driven handle	3 382 23 + 4 210 74	-	-	300	3 382 72
		Vertical	With side motor-driven handle	3 382 23 + 4 210 69	-	-	300	3 382 72
	36 modules wide	Vertical	Without side motor-driven handle	3 382 26 + 4 210 72	-	-	400	3 382 82
		Vertical	With e.l.c.bs without side motor-driven handle	3 382 26 + 4 210 74	-	-	300	3 382 73
		Vertical	With side motor-driven handle	3 382 26 + 4 210 69	-	-	300	3 382 73
		Vertical	Without side motor-driven handle	3 382 26 + 4 210 72	-	-	300	3 382 73
		Vertical	With e.l.c.bs without side motor-driven handle	3 382 26 + 4 210 74	-	-	300	3 382 73
		Vertical	With side motor-driven handle	3 382 26 + 4 210 69	-	-	300	3 382 73
<b>FIXING ON PLATE</b>				<b>FIXING ON PLATE</b>				
DPX <sup>3</sup> 160	16 modules wide	Horizontal/side uprights	3P	-	3 383 00	-	150	3 383 51
			4P with or without e.l.c.bs	-	3 383 01	-	150	3 383 51
	24 modules wide	Horizontal/side uprights	3P	-	3 383 04	-	150	3 383 54
			4P with or without e.l.c.bs	-	3 383 04	-	150	3 383 54
	36 modules wide	Horizontal/side uprights	3P	-	3 383 07	-	150	3 383 57
			4P with or without e.l.c.bs	-	3 383 07	-	150	3 383 57
	16 modules wide	Horizontal/central upright	3P	-	3 396 20	-	100	3 383 50
			4P with or without e.l.c.bs	-	3 396 10	-	150	3 383 51
	24 modules wide	Horizontal/central upright	3P	-	3 396 20	-	100	3 383 53
			4P with or without e.l.c.bs	-	3 396 10	-	150	3 383 54
	36 modules wide	Horizontal/central upright	3P	-	3 396 20	-	100	3 383 56
			4P with or without e.l.c.bs	-	3 396 10	-	150	3 383 57
	16 modules wide	Vertical	3P or 4P	-	3 383 20	-	300	3 382 71
			4P with e.l.c.bs	-	3 383 21	-	300	3 382 71
	24 modules wide	Vertical	3P	-	3 383 23	-	300	3 382 72
			4P	-	3 383 24	-	300	3 382 72
	36 modules wide	Vertical	3P	-	3 383 25	-	300	3 382 72
			4P with e.l.c.bs	-	3 383 26	-	300	3 382 73
36 modules wide	Vertical	3P	-	3 383 26	-	300	3 382 73	
		4P	-	3 383 27	-	300	3 382 73	
36 modules wide	Vertical	3P	-	3 383 28	-	300	3 382 73	
		4P with e.l.c.bs	-	3 383 28	-	300	3 382 73	
DPX <sup>3</sup> 250	16 modules wide	Horizontal/side uprights	3P	-	3 384 01	-	150	3 384 50
			4P with or without e.l.c.bs	-	3 384 01	-	200	3 384 51
	24 modules wide	Horizontal/side uprights	3P	-	3 384 04	-	150	3 384 53
			4P with or without e.l.c.bs	-	3 384 04	-	200	3 384 54
	36 modules wide	Horizontal/side uprights	3P	-	3 384 07	-	150	3 384 56
			4P with or without e.l.c.bs	-	3 384 07	-	200	3 384 57
	16 modules wide	Horizontal/central upright	3P	-	3 396 21	-	150	3 384 50
			4P with or without e.l.c.bs	-	3 396 11	-	200	3 384 51
	24 modules wide	Horizontal/central upright	3P	-	3 396 21	-	150	3 384 53
			4P with or without e.l.c.bs	-	3 396 11	-	200	3 384 54
	36 modules wide	Horizontal/central upright	3P	-	3 396 21	-	150	3 384 56
			4P with or without e.l.c.bs	-	3 396 11	-	200	3 384 57
	16 modules wide	Vertical	3P or 4P	-	3 384 20	-	300	3 382 71
			4P with e.l.c.bs	-	3 384 21	-	300	3 382 71
	24 modules wide	Vertical	3P	-	3 384 23	-	300	3 382 72
			4P	-	3 384 24	-	300	3 382 72
	36 modules wide	Vertical	3P	-	3 384 25	-	300	3 382 72
			4P with e.l.c.bs	-	3 384 25	-	300	3 382 72
36 modules wide	Vertical	3P	-	3 384 26	-	300	3 382 73	
		4P	-	3 384 27	-	300	3 382 73	
36 modules wide	Vertical	3P	-	3 384 28	-	300	3 382 73	
		4P with e.l.c.bs	-	3 384 28	-	300	3 382 73	