

Distribution enclosures XL³ 4000

Enclosures	"Roof-base" assembly	Structural uprights	Plinths	Functional uprights	Faceplate supports		Int. cable sleeves crosspcs	Int. cable sleeves fr. covers	Rear panels	Side panels	Doors			
					fixed	pivoting					Curved Metal	Curved Glass	Flat Metal	Flat Glass
Height 2000 or 2200 mm Width x Depth														
 725 x 425	0 205 04	0 205 00 0 208 50 ⁽²⁾	0 205 14	0 205 12 0 208 52 ⁽²⁾	0 205 58 0 208 55 ⁽²⁾	0 205 68	-	-	0 205 42 0 208 58 ⁽²⁾	0 205 41 0 208 57 ⁽²⁾	0 205 54 0 208 61 ⁽²⁾	0 205 64 0 208 63 ⁽²⁾	0 205 74	0 205 84
 725 x 725	0 205 05	0 205 00 0 208 50 ⁽²⁾	0 205 15	0 205 13 0 208 53 ⁽²⁾	0 205 58 0 208 55 ⁽²⁾	0 205 68	-	-	0 205 42 0 208 58 ⁽²⁾	0 205 42 0 208 58 ⁽²⁾	0 205 54 0 208 61 ⁽²⁾	0 205 64 0 208 63 ⁽²⁾	0 205 74	0 205 84
 725 x 975	0 205 06	0 205 00 0 208 50 ⁽²⁾	0 205 18	0 205 13 0 208 53 ⁽²⁾	0 205 58 0 208 55 ⁽²⁾	0 205 68	-	-	0 205 42 0 208 58 ⁽²⁾	0 205 43 0 208 59 ⁽²⁾	0 205 54 0 208 61 ⁽²⁾	0 205 64 0 208 63 ⁽²⁾	0 205 74	0 205 84
 975 x 475 ⁽¹⁾	0 205 07	0 205 00 0 208 50 ⁽²⁾	0 205 17	0 205 12 0 205 16 0 208 54 ⁽²⁾	0 205 58 0 208 55 ⁽²⁾ 0 208 56 ⁽²⁾	0 205 69 0 205 79	0 205 21	0 205 47	0 205 43 0 208 59 ⁽²⁾	0 205 41 0 208 57 ⁽²⁾	0 205 57 0 208 62 ⁽²⁾	0 205 67 0 208 64 ⁽²⁾	0 205 77	0 205 87
 975 x 725 ⁽¹⁾	0 205 08	0 205 00 0 208 50 ⁽²⁾	0 205 18	0 205 13 0 205 16 0 208 54 ⁽²⁾	0 205 58 0 208 55 ⁽²⁾ 0 208 56 ⁽²⁾	0 205 69 0 205 79	0 205 22	0 205 47	0 205 43 0 208 59 ⁽²⁾	0 205 42 0 208 58 ⁽²⁾	0 205 57 0 208 62 ⁽²⁾	0 205 67 0 208 64 ⁽²⁾	0 205 77	0 205 87
 975 x 975 ⁽¹⁾	0 205 09	0 205 00 0 208 50 ⁽²⁾	0 205 19	0 205 13 0 205 16 0 208 54 ⁽²⁾	0 205 58 0 208 55 ⁽²⁾ 0 208 56 ⁽²⁾	0 205 69 0 205 79	0 205 23	0 205 47	0 205 43 0 208 59 ⁽²⁾	0 205 43 0 208 59 ⁽²⁾	0 205 57 0 208 62 ⁽²⁾	0 205 67 0 208 64 ⁽²⁾	0 205 77	0 205 87

External cable sleeves	"Roof-base" assemble	Structural uprights	Plinths	Front covers	Rear panels	Side panels	Metal doors
Height 2000 or 2200 mm Width x Depth							
 475 x 475	0 205 01	0 205 00 0 208 50 ⁽²⁾	0 205 11	0 205 48 0 208 67 ⁽²⁾	0 205 41 0 208 57 ⁽²⁾	0 205 41 0 208 57 ⁽²⁾	0 205 71 0 208 65 ⁽²⁾
 475 x 725	0 205 02	0 205 00 0 208 50 ⁽²⁾	0 205 14	0 205 48 0 208 67 ⁽²⁾	0 205 41 0 208 57 ⁽²⁾	0 205 42 0 208 58 ⁽²⁾	0 205 71 0 208 65 ⁽²⁾
 475 x 975	0 205 03	0 205 00 0 208 50 ⁽²⁾	0 205 17	0 205 48 0 208 67 ⁽²⁾	0 205 41 0 208 57 ⁽²⁾	0 205 43 0 208 59 ⁽²⁾	0 205 71 0 208 65 ⁽²⁾

1: With internal cable sleeve
2: For enclosure height 2200 mm