

## P 17 Tempra Pro IP 66/67 LV 63 and 125 A

## Foldable frame for P 17 worksites combined units



5 555 59



5 555 89



5 555 29



5 555 09

Easy connection  
disconnection

Technical characteristics **see e-catalogue**



0 577 43 equipped with a P 17 worksite combined unit

Dimensions **p. 388**

Pack	Cat.Nos		Surface mounting sockets
	63 A	125 A	<b>200/250 V~</b>
2	5 555 54		2P+E
2	5 555 55		3P+E
2	5 555 56		3P+N+E
			<b>380/415 V~</b>
2   1	5 555 58	5 556 58	3P+E
2   1	5 555 59	5 556 59	3P+N+E

Pack	Cat.Nos	Foldable frame
1	0 577 43	For floor cabinets The unit can be fixed on the frame without opening the unit The unit equipped with its frame can be wall or floor-mounted Can be folded for easy transport and storage

Pack	Cat.Nos		Panel mounting sockets
	63 A	125 A	<b>200/250 V~</b>
2	5 555 84		2P+E
2	5 555 85		3P+E
2	5 555 86		3P+N+E
			<b>380/415 V~</b>
2   1	5 555 88	5 556 88	3P+E
2   1	5 555 89	5 556 89	3P+N+E

Can be fixed on the faceplates  
Cat.Nos 0 577 17/19 (p. 346)

Pack	Cat.Nos		Straight plugs
	63 A	125 A	<b>200/250 V~</b>
2	5 555 24		2P+E
2	5 555 25		3P+E
2	5 555 26		3P+N+E
			<b>380/415 V~</b>
2   1	5 555 28	5 556 28	3P+E
2   1	5 555 29	5 556 29	3P+N+E

Pack	Cat.Nos		Mobile sockets
	63 A	125 A	<b>200/250 V~</b>
2	5 555 04		2P+E
2	5 555 05		3P+E
2	5 555 06		3P+N+E
			<b>380/415 V~</b>
2   1	5 555 08	5 556 08	3P+E
2   1	5 555 09	5 556 09	3P+N+E

Pack	Cat.Nos		Appliance inlets
	63 A	125 A	<b>200/250 V~</b>
2	5 555 14		2P+E
			<b>380/415 V~</b>
2   1	5 555 18	5 556 18	3P+E
2   1	5 555 19	5 556 19	3P+N+E