Llegrand

Hotel equipment KNX wiring devices













2 modules

e Co

Arteor version To be equipped with Arteor support frames and plates (p. 480-487)

Valena Life version To be equipped with Valena Life plates (p. 526)

Valena Allure version To be equipped with Valena Allure plates (p. 527)

0 674 64

N

7 521 47

7 527 47

1

1



0 674 64 + plate Cube 5 714 02

5 735 02 + plate Graphite 5 756 12

لو

Support frame and plate selection charts **p. 480-487** and **526-527** Key covers selection chart **p. 413-414**

Directly connected to the KNX BUS (supplied with KNX connectors) Programming through ETS software

Pack	Cat.Nos	KNX control mechanisms	Pack	Cat.Nos	Room Controller Units
		For lighting control (ON/OFF, dimming, scenario), shutters and slats controls and automation control Equipped with programmable LEDs (12 colours available) to indicate the status of the loads and provide system and alarm status feedback			Power modules equipped with output contacts for controlling: - different types of of ON/OFF load (lighting, roller shutters, contactors, motors, etc.) - a DALI dimming output for 64 ballasts max. Loads are managed by the controls to which they
1	0 675 71	Mechanism to be equipped - 4 actuation points 2 modules To be equipped with : - Arteor key covers (p. 413) support frames and plates (p. 480-487) or			are linked: either by BUS/KNX controls, or by wired connection input terminals (switches, push-buttons, volt-free contacts). Multiphase connection and consumption
		- Valena Life/Allure cover plates (p. 414) plates (p. 526-527)	1	0 484 18	measurement. 8 inputs - 10 outputs 8 DIN modules 17.5 mm
		Arteor version - 4 actuation points With label holder To be equipped with support frames and plates	1	0 484 22	16 inputs - 16 outputs 12 DIN modules 17.5 mm
1	5 742 03	(p. 480 to 487)			KNX thermostat
1	5 744 04	Magnesium - square version			For fan coil units: 2 tubes, 2 tubes + 2 wires and 4 tubes for heating and/or air conditioning For controlling on/off valves, 3 positions and 3 speeds
1 1	5 735 02 5 735 03	 White - round version Magnesium - round version 			(fan): comfort, economy and protection with manual or automatic selection. Adjustment accuracy + 0.5 °C 2 multi-function inputs for window contacts, summer/ winter changeover, etc
		Touch control mechanisms - 4 actuation points			Backlit display
		Supplied with glass plates Upon request, customization of plates possible with any other standard symbols (please contact us)	1	0 490 31	Operating voltage 230 V~. Supplied complete with dedicated flush-mounting box
1 1	5 735 04 5 735 05	○ White ● Black			
					Temperature control
1	5 735 12	Touch control mechanisms - 6 actuation points Supplied with glass plates Upon request, customization of plates possible with any other standard symbols (please contact us)			1,6' backlight display with 4 push-buttons and embedded a temperature probe Used to manage different types of heating/cooling system (FCU, heating/cooling valve, fan, electric load,) in combination through KNX with dedicated
1	5 735 13	• Black			HVAC controller (for details see dedicated KNX brochure) - monitoring the ambient temperature with desired unit
					-adjustment of the temperature set-point and/or fan speed -selection of operating mode(comfort, protection) To be installed in flush-mounting boxes 2 modules