

Arteor™ load selection charts

Load selection charts

	Cat.Nos	Universal							
		Leading edge				Trailing edge			
		Incandescent lamp		Halogen lamp		ELV halogen with ferromagnetic transformer		ELV halogen with electronic transformer	
	110 V	230 V	110 V	230 V	110 V	230 V	110 V	230 V	
Sensitive switches	5 720 51 5 734 55 5 725 51 5 736 55	500 W	1000 W	500 W	1000 W	250 VA	500 VA	250 VA	500 VA
Dimmers	5 722 13 5 727 13	200 W	400 W	200 W	400 W	200 VA	400 VA		
	5 735 01 5 737 01 5 722 40 5 727 40	500 W	1000 W	500 W	1000 W	500 VA	1000 VA	300 VA	600 VA
	5 722 39 5 727 39 5 743 19 5 743 39	200 W	400 W	200 W	400 W	200 VA	400 VA	200 VA	400 VA
Motion sensors	5 740 47 5 740 97	1000 W	2000 W	1000 W	2000 W	500 VA	1000 VA	500 VA	1000 VA
	5 740 05 5 740 55	-	400 W	-	400 W	-	2000 VA	-	200 VA
	5 740 09 5 740 59	125 W	250 W	125 W	250 W	125 VA	250 VA	125 VA	250 VA

	Cat.Nos	Universal					
		Fluorescent tube		Compact fluorescent lamp		LED	
		110 V	230 V	110 V	230 V	110 V	230 V
Sensitive switches	5 720 51 5 734 55 5 725 51 5 736 55	250 VA	500 VA	250 VA	500 VA	250 VA	500 VA
Dimmers	5 722 39 5 727 39 5 743 19 5 743 39	100 VA	200 VA	Dimmable 37 W 10 lamps max	Dimmable 75 W 10 lamps max	Dimmable 37 W 10 lamps max	Dimmable 75 W 10 lamps max
Motion sensors	5 740 47 5 740 97	300 W	720 W	250 VA	500 VA	250 VA	500 VA
	5 740 05 5 740 55	-	150 VA	-	50 W	-	50 W
	5 740 09 5 740 59	125 VA	250 VA	50 W	100 W	50 W	100 W

	Cat.Nos	Ballasts 1-10 V		Reducer motor for shutters	
		110 V	230 V	110 V	230 V
Sensitive switches	5 720 51 5 734 55 5 725 51 5 736 55			50 VA	100 VA
Dimmers	5 722 38 5 727 38 5 743 18 5 743 38	300 VA 40 mA	600 VA 40 mA		