

Valena™ IN'MATIC mechanisms

USB charging sockets



7 531 12 + 7 540 71
(Valena Life - Terracotta)



7 549 95 + 7 543 61
(Valena Allure - Fiora)



7 531 14 + 7 543 91
(Valena Allure - Aluminium)



7 549 97 + 7 543 91
(Allure Aluminium)

Technical characteristics [see e-catalogue](#)

Valena In'Matic mechanisms are supplied with metal support, for claw or screw mounting. IP 2X protection. Supplied with mounted dust protection transparent shield. Packaged in boxes (except Valena Life double USB charging socket - in flowpack)

Pack	Cat.Nos	Type-A USB charging sockets
		For recharging portable devices Conform to IEC 62684-2011-01 Surge protection > 1 kV Power supply standby mode consumption: < 0.06 W Power supply AC/DC efficiency at highest level (VI) 2x2.5 mm ² screw terminals Class II SELV Supplied cordless Double USB sockets - 5 V - 2.4 A - 12 W For fast charging smartphones and tablet PC
5	7 531 12	White Valena Life
5	7 532 12	Ivory Valena Life
5	7 533 12	Aluminium Valena Life
1	7 549 95	White Valena Allure
1	7 549 96	Ivory Valena Allure
1	7 549 97	Black Valena Allure
1	7 549 98	Pearl Valena Allure
1	7 549 99	
		2P+E + USB Type C mixed socket outlet Mixed socket composed of: - 2 P+E socket outlet - 16 A - 250 V~ - single USB socket - 5 V - 1.5 A - 7.5 W Supplied with support (spacing 71 mm) and cover plate
1	7 531 35	White Valena Life
1	7 532 35	Ivory Valena Life
1	7 533 35	Aluminium Valena Life
		Wireless power stations with Type-A USB 1 A charger with one 3 A/12 W USB port to power a second device To be fitted with a support and a plate Comes with 2 induction antennae for fast intuitive smartphone charging Recognition area: 50 x 80 mm Plate at an angle of 10° with non-slip coating to hold the terminal safely in place during charging Dimensions: 136.5 x 70 x 56.5 mm Anti-theft lock function Can be mounted in multiple horizontal positions
1	7 531 14	White Valena Life
1	7 551 14	White Valena Allure

Pack	Cat.Nos	Type-A USB charging sockets (continued)
		Supports for portable device during charging Multigang installation with 2 x USB charging sockets or with a 2P+E socket and a mobile charger Flat frame: does not require a flush mounting box Fixing with screws or adhesive on all types of surface Prevent device from any risk of falling and allow secure use of device while charging Wall-mounting clamp For 1 portable device
1	7 549 10	White Valena Life
1	7 549 11	Ivory Valena Life
		Type-C USB charging sockets 5 V - 3 A - 15 W Universal charger for portable devices Conform to CEI 62680-1-3 Certified USB-IF Surge protection > 1 kV Power supply standby mode consumption: < 0.07 W Power supply AC/DC efficiency at highest (VI) 2x2.5 mm ² screw terminals Class II SELV Supplied cordless
		Double USB Type C+C sockets
5	7 531 07	White Valena Life
5	7 532 07	Ivory Valena Life
5	7 533 07	Aluminium Valena Life
1	7 553 45	White Valena Allure
1	7 553 46	Ivory Valena Allure
1	7 553 47	Aluminium Valena Allure
		Double USB Type A + Type C sockets
5	7 531 06	White Valena Life
5	7 532 06	Ivory Valena Life
5	7 533 06	Aluminium Valena Life
1	7 549 65	White Valena Allure
1	7 549 66	Ivory Valena Allure
1	7 549 67	Aluminium Valena Allure

See the video on USB charging sockets benefits

