

Valena™ IN'MATIC mechanisms

LED lamps



7 520 01 + 7 550 02
+ 7 541 31 + 0 676 84
(Valena Life - Aluminium)



7 520 05 + 7 550 20
+ 7 540 01 + 2 x 0 676 84
(Valena Life - White)



7 520 06 + 0 676 86
+ 7 550 85 + 7 543 01
(Valena Allure - White)

All lamps in Valena Life and Valena Allure range devices have low consumption LED technology. After clipping in the rocker, all lamps light up blue

Pack	Cat.Nos	LED lamps for illuminated functions
10	0 676 84	Plug-in LED lamp for illuminated one-way switch and push-button 230 V~ - Consumption 0.15 mA
10	0 676 86	Plug-in LED lamp for illuminated two-way switch 230 V~ - Consumption 0.15 mA
10	6 650 90	LED lamp to be wired for illuminated intermediate switch 230 V~ - Consumption 0.15 mA
10	0 676 87	Plug-in LED lamp for 12-48 V illuminated push-buttons 12-24-48 V
LED lamps for indicator functions		
10	0 676 88	Plug-in LED lamp for two-way switch with indicator and neutral terminal 230 V~ - Consumption 3 mA
10	6 650 91	LED lamp to be wired for indicator functions 230 V~ - Consumption 3 mA
10	0 676 64	LED lamp to be wired for indicator socket 230 V~ - Consumption 3 mA
Valena Allure specific LED lamps		
Blue coloured surround light between the rocker and the plate		
5	7 520 57	Plug-in LED lamp for illuminated two-way switch 230 V~ - Consumption 0.15 mA
5	7 520 58	Plug-in LED lamp for two-way switch with indicator and neutral 230 V~ - Consumption 3 mA

Valena™ IN'MATIC mechanisms

technical alarms



7 521 41
+ 7 540 71
(Valena Life + Terracotta)



7 522 37 + 7 541 81
(Valena Life - Light wood)

Valena In'Matic mechanisms are with metal support, claw or screw mounting. Supplied with cover plates and to be equipped with plates of Valena Life. Supplied with mounted dust protection transparent shield Packaged in boxes

Pack	Cat.Nos	Technical alarms
Gas detectors for propane, butane		
Indicates the presence of gas via a LED and audible alarm signal 85 dB at 1 m Power supply 12 V~ Cat.Nos 7 521 39, 7 522 39, 7 523 39		
1	7 521 36	□ White Valena Life
1	7 522 36	■ Ivory Valena Life
1	7 523 36	□ Aluminium Valena Life
Gas detectors for methane		
Power supply 12 V~ Cat.Nos 7 521 39, 7 522 39, 7 523 39		
1	7 521 37	□ White Valena Life
1	7 522 37	■ Ivory Valena Life
1	7 523 37	□ Aluminium Valena Life
Water leak detectors		
LED indication of the presence of a conducting liquid The height at which the sensor is installed determines the level of flooding detected Consumption: - 0.1 mA in stand-by mode - 25 mA in alarm mode Supplied with sensor and 2 m length cable. Power supply 12 V~ Cat.Nos 7 521 39, 7 522 39, 7 523 39 Consumption in standby mode: 0.1 mA		
1	7 521 41	□ White Valena Life
1	7 522 41	■ Ivory Valena Life
1	7 523 41	□ Aluminium Valena Life