




Valena™ Life

cover plate selection charts (continued)

Functions	VALENA IN'MATIC™ MECHANISMS	VALENA™ LIFE COVER PLATES		
		White 	Ivory 	Aluminium 
2P SOCKET OUTLETS 16 A - 250 V~				
2P socket with shutters, automatic terminals	7 530 16	7 549 70	7 549 71	7 549 72
GERMAN STANDARD SOCKET OUTLETS 16 A - 250 V~				
2P+E socket with shutters, automatic terminals	7 530 20	7 552 00 or 7 548 40 (with flap) or 7 548 50 (with indicator)	7 552 01 or 7 548 41 (with flap) or 7 548 51 (with indicator)	7 552 02 or 7 548 42 (with flap) or 7 548 52 (with indicator)
2P+E socket, with shutters, screw terminals	7 530 24			
2P+E socket, automatic terminals	7 530 21	7 552 00 or 7 548 40 (with flap) or 7 548 50 (with indicator)	7 552 01 or 7 548 41 (with flap) or 7 548 51 (with indicator)	7 552 02 or 7 548 42 (with flap) or 7 548 52 (with indicator)
2P+E socket, screw terminals	7 530 25			
GERMAN STANDARD DOUBLE SOCKET OUTLETS 16 A - 250 V~				
2x2P+E socket with shutters, automatic terminals	7 530 26	7 549 50	7 549 51	7 549 52
2x2P+E socket, automatic terminals	7 530 27			
2x2P+E socket plate adaptor		7 542 25	7 542 35	7 542 45
ACCESSORIES				
Cable outlet with terminals	7 530 33	7 547 30	7 547 31	7 547 32
Cable outlet without terminals	7 530 34			
Surface-mounting box 1 gang		7 541 91	7 542 01	7 542 11
Surface-mounting box 2 gang		7 541 92	7 542 02	7 542 12
Support frame 4x2 modules with plate		7 521 45		7 523 45
Support frame 2x4x2 modules with plate		7 521 46		7 523 46
Blanking plate		7 551 80	7 551 81	7 551 82
SOUND DIFFUSION				
Source input with power supply	-	7 554 50	7 554 51	7 554 52
Bluetooth module	-	7 554 30	7 554 31	7 554 32