






Valena™ Allure

cover plate selection charts (continued)

Functions	VALENA IN'MATIC™ MECH.	VALENA™ ALLURE COVER PLATES				
		White 	Ivory 	Aluminium 	Black 	Pearl 
2P SOCKET OUTLETS 16 A - 250 V~						
2P socket with shutters, automatic terminals	7 530 16	7 549 75	7 549 76	7 549 77	7 549 78	7 549 79
GERMAN STANDARD SOCKET OUTLETS 16 A - 250 V~						
2P+E socket with shutters, automatic terminals	7 530 20	7 552 05 or 7 548 45 (with flap)	7 552 06 or 7 548 46 (with flap)	7 552 07 or 7 548 47 (with flap)	7 552 08 or 7 548 48 (with flap)	7 552 09 or 7 548 49 (with flap)
2P+E socket, with shutters, screw terminals	7 530 24	7 548 55 (with indicator)	7 548 56 (with indicator)	7 548 57 (with indicator)	7 548 58 (with indicator)	7 548 59 (with indicator)
2P+E socket, automatic terminals	7 530 21	7 552 05 or 7 548 45 (with flap)	7 552 06 or 7 548 46 (with flap)	7 552 07 or 7 548 47 (with flap)	7 552 08 or 7 548 48 (with flap)	7 552 09 or 7 548 49 (with flap)
2P+E socket, screw terminals	7 530 25	7 548 55 (with indicator)	7 548 56 (with indicator)	7 548 57 (with indicator)	7 548 58 (with indicator)	7 548 59 (with indicator)
GERMAN STANDARD DOUBLE SOCKET OUTLETS 16 A - 250 V~						
2x2P+E socket with shutters, automatic terminals	7 530 26	7 549 55 ⁽¹⁾	7 549 56 ⁽¹⁾	7 549 57 ⁽¹⁾	7 549 58 ⁽¹⁾	7 549 59 ⁽¹⁾
2x2P+E socket, automatic terminals	7 530 27					
ACCESSORIES						
Cable outlet with terminals	7 530 33	7 550 55	7 550 56	7 550 57		
Cable outlet without terminals	7 530 34					
Surface-mounting box 1 gang		7 555 51	7 555 61	7 555 71		
Surface-mounting box 2 gang		7 555 52	7 555 62	7 555 72		
Blanking plate		7 551 85	7 551 86	7 551 87		

1: Monobloc cover + plate

2: To be used with Power supply in false ceiling for Bluetooth module Cat.No 0 673 22 (p. 474)