

Valena™ Life

socket outlets with cover plate (continued)



7 531 26 + 7 542 21
(White)



7 533 26 + 7 542 41
(Aluminium)

Valena In'Matic mechanisms supplied with cover plates and support frames. To be equipped with plates IP 2X protection. Supplied with mounted dust protection transparent shield
Flowpack packaging: robust protection to ensure optimum operation

Pack	Cat.Nos	German standard double socket outlets 16 A - 250 V~
		Automatic terminals
		2x2P+E sockets with shutters
5	7 531 26	<input type="checkbox"/> White
5	7 532 26	<input type="checkbox"/> Ivory
5	7 533 26	<input type="checkbox"/> Aluminium
		2x2P+E sockets
5	7 531 27	<input type="checkbox"/> White
5	7 532 27	<input type="checkbox"/> Ivory
5	7 533 27	<input type="checkbox"/> Aluminium
		2x2P+E sockets plate adaptor
		To be used for creating multigang installations of single functions with double sockets (for example RJ 45 sockets, TV sockets, etc)
5	7 542 25	<input type="checkbox"/> White
5	7 542 35	<input type="checkbox"/> Ivory
5	7 542 45	<input type="checkbox"/> Aluminium

For multigang plates for 2x2P+E sockets, please refer to the selection chart on **p. 526**

Valena™ Life

USB charging sockets with cover plate



7 531 12 + 7 540 71
(Valena Life - Terracotta)



7 531 14 + 0 775 98
+ 7 541 31 (Aluminium)

Valena In'Matic mechanisms supplied with cover plates and support frames. To be equipped with plates IP 2X protection. Supplied with mounted dust protection transparent shield
Flowpack packaging: robust protection to ensure optimum operation

Pack	Cat.Nos	Type-A USB charging sockets
		For recharging mobile devices Conform to IEC 62684-2011-01 Surge protection > 1 kV Power supply standby mode consumption: < 0.07 W Power supply AC/DC efficiency at highest level (VI) 2x2.5 mm ² screw terminals Class II SELV Supplied cordless
		Double USB sockets - 5 V - 2.4 A - 12 W
		For charging smartphones and tablet PC
5	7 531 12	<input type="checkbox"/> White
5	7 532 12	<input type="checkbox"/> Ivory
5	7 533 12	<input type="checkbox"/> Aluminium
		2P+E + USB Type C mixed socket outlet
		Mixed socket composed of: - 2 P+E socket outlet - 16 A - 250 V~ - single USB socket - 5 V - 1.5 A - 7.5 W Supplied with support (spacing 71 mm) and cover plate
1	N 7 531 35	<input type="checkbox"/> White Valena Life
1	7 532 35	<input type="checkbox"/> Ivory Valena Life
1	7 533 35	<input type="checkbox"/> Aluminium Valena Life
		Wireless power stations with USB Type-A
		1 A charger with one 2.4 A/12 W USB port to power a second device To be fitted with a support and a plate Comes with 2 induction antennae for fast intuitive smartphone charging Recognition area: 50 x 80 mm Plate at an angle of 10° with non-slip coating to hold the terminal safely in place during charging Dimensions: 136.5 x 70 x 56.5 mm Anti-theft lock function Can be mounted in multiple horizontal positions
1	N 7 531 14	<input type="checkbox"/> White Valena Life

Other wireless charging stations **p. 886**