

## Valena™ Life

USB charging sockets with cover plate (continued)



## Valena™ Life

accessories with cover plate



7 531 06 + 7 540 31  
(White Chrome)

Valena In'Matic mechanisms supplied with cover plates and support frames. To be equipped with plates. IP 2X protection  
Supplied with mounted dust protection transparent shield  
Flowpack packaging: robust protection to ensure optimum operation



7 531 33 + 7 540 01  
(White)

Valena In'Matic mechanisms supplied with cover plates and support frames. To be equipped with plates. IP 2X protection  
Supplied with mounted dust protection transparent shield  
Flowpack packaging: robust protection to ensure optimum operation

### Pack Cat.Nos Type-A USB charging sockets (continued)

Pack	Cat.Nos	Type-A USB charging sockets (continued)
		<b>Supports for portable device during charging</b>
		Multigang installation with 2 x USB charging sockets or with a 2P+E socket and a mobile charger Flat frame: does not require a flush mounting box Fixing with screws or adhesive on all types of surface Prevent device from any risk of falling and allow secure use of device while charging Wall-mounting clamp For 1 portable device
1	7 549 10	White
1	7 549 11	Ivory

### Type-C USB charging sockets

		5 V - 3 A - 15 W Universal charger for portable devices Conform to CEI 62680-1-3 Certified USB-IF Surge protection > 1 kV Power supply standby mode consumption: < 0.07 W Power supply AC/DC efficiency at highest (VI) 2x2.5 mm <sup>2</sup> screw terminals Class II SELV Supplied cordless
--	--	--

#### Double USB Type C+C sockets

5	7 531 07	White
5	7 532 07	Ivory
5	7 533 07	Aluminium

#### Double USB Type A + Type C sockets

5	7 531 06	White
5	7 532 06	Ivory
5	7 533 06	Aluminium

### Pack Cat.Nos Accessories

Pack	Cat.Nos	Accessories
		<b>Cable outlet with terminals</b>
		With 5 terminals to take 2.5 mm <sup>2</sup> cables Maximum cable diameter: 12 mm With cable grip
5	7 531 33	White
5	7 532 33	Ivory
5	7 533 33	Aluminium
		<b>Cable outlet without terminals</b>
		Maximum cable diameter: 12 mm With cable grip
5	7 531 34	White
5	7 532 34	Ivory
5	7 533 34	Aluminium