

Forix™

IP 2X surface-mounting socket outlets, telephone, data and TV sockets



7 824 17



7 824 24



7 824 15



7 824 29

Conform to IEC standard
 Complete mechanisms supplied with rocker and cover plate. Screw terminals IP2X
 2 finishes:
 - White RAL R903 - Glossy finish
 - Ivory RAL R113 - Glossy finish

Pack Cat.Nos French standard socket outlets 16 A - 250 V~

20	7 824 17	2P+E with shutters for child protection <ul style="list-style-type: none"> ○ White ● Ivory
20	7 824 47	
10	7 824 39	2 x 2P+E with shutters for child protection Inclined 45° horizontal or vertical mounting <ul style="list-style-type: none"> ○ White ● Ivory
10	7 824 69	

20	7 824 14	RJ 11 telephone sockets Automatic connection by piercing the insulating material Supplied with a tool <ul style="list-style-type: none"> ○ White ● Ivory
20	7 824 44	

20	7 824 21	RJ 11 telephone socket and RJ 45 cat. 5e - UTP socket Automatic connection by piercing the insulating material Supplied with a tool <ul style="list-style-type: none"> ○ White ● Ivory
20	7 824 51	

20	7 824 24	RJ 45 sockets cat. 5e - UTP Automatic connection by piercing the insulating material Supplied with a tool <ul style="list-style-type: none"> ○ White ● Ivory
20	7 824 54	
20	7 824 28	2 x RJ 45 <ul style="list-style-type: none"> ○ White

Pack Cat.Nos RJ 45 keystone connector adaptor

20	7 824 26	<ul style="list-style-type: none"> ○ White
----	----------	---

20	7 824 15	Television sockets Terminal TV socket Male connector Ø9.52 mm <ul style="list-style-type: none"> ○ White ● Ivory
20	7 824 45	

20	7 824 16	Wire outlets Supplied with cable ties <ul style="list-style-type: none"> ○ White ● Ivory
20	7 824 46	

10	7 824 29	Dismatic - 20 A For protection and control of air-conditioning system Single pole 220 V/380 V thermal MCB <ul style="list-style-type: none"> ○ White
----	----------	---

50	7 824 57	Lamp 230 V - Consumption 3.4 mA
----	----------	---