



2 810 40



2 810 84



2 810 75



2 810 90

Polycarbonate front cover plates with a matt finish. Compact mechanism for greater wiring space. Supplied with 2 screws M 3.5 for BS boxes
Supplied complete with plate. Dim.: 86 x 86 mm

Pack	Cat.Nos		Pack	Cat.Nos	
		Push-buttons 10 A - 250 V\sim			Leading edge dimmers (continued)
10	2 810 41	Conform to BS EN 60669-1 N/O contact (push to make) ○ White 			Rotary dimmer 60-1000 W (230 V) 60-500 W (127 V) for incandescent and halogen lamps 60-600 VA (230 V) 60-300 VA (127 V) for halogen lamps with electronic transformer with leading edge behaviour 60-1000 VA (230 V) 60-500 W (127 V) for halogen lamps with ferromagnetic transformers ○ White
10	2 810 40	N/O contact with bell symbol ○ White 	1	2 810 85	
		2 gang Push-button 4A 250V\sim			Automatic switch
10	2 810 42	Conform to BS EN 60669-1 N/O contact (push to make) ○ White 	1	2 810 90	Conform to BS EN 60669-2-1 IR movement detector Horizontal detection angle 180° Luminosity threshold: 43 to 1614 lux Temporization: 20 s - 15 min Detection range: max. 12 m Compatible load: 25 - 200 W for incandescent and halogen lamps 230 V \sim ○ White
		RLC + LED dimmer			Fan speed controls
1	2 810 86	Rotary dimmer without neutral Conform to BS EN 60669-2-1 100-240 V \sim for all types of dimmable lamps: - dimmable LED: 5 to 75 W (10 lamps max.) - dimmable compact fluorescent lamps: 5 to 75 W (10 lamps max.) - fluorescent tube with ballast: 5 to 300 VA - halogen and incandescent: 5 to 300 W - electronic or ferromagnetic transformers: 5 to 300 VA When switched on, gradually (2 seconds) lights up at the level set before last switch off	1	2 810 82	Conform to BS EN 60669-2-1 5-speed fan control 100 W for fan with overall diameter 48" ○ White
1	0 401 49	Active compensator Allows to ensure compatibility of 2-wire electronic lighting controls without neutral with all available types of loads (LEDs, compact fluorescent lamps ELV halogen lamps with electronic or conventional ballast, 230 V halogen lamps, fluorescent tubes, incandescent lamps) Consumption: 0.4 W			Cooker control unit 45 A - 250 V\sim
		Leading edge dimmers	5	2 810 75	Conform to BS 4177 45 A DP switch + 13 A switched socket outlet with red indicator Dim.: 146 x 86 mm ○ White
1	2 810 80	Conform to BS EN 60669-2-1 Rotary control dimmer 60-500 W for incandescent and halogen lamps 230 V \sim 60-500 VA ELV halogen lamps with ferromagnetic transformer and compensator Cat.No 0 401 39 ○ White 			
1	2 810 84	Rotary control dimmer + switch 60-500 W for incandescent and halogen lamps 230 V \sim 60-200 VA ELV halogen lamps with ferromagnetic transformer and compensator Cat.No 0 401 39 ○ White 			