

Synergy™

double pole switches - white



7 301 10

7 300 22

Front plates: white thermoset
Terminal screws captive and backed off ready for cabling - large angled terminal entries
Compact mechanism for maximised wiring space
Supplied with faceplate screw caps

Pack	Cat.Nos	Double pole switches 20 A - 250 V~
10	7 300 10	Conform to BS EN 60669-1 For flush-mounting, back box to be min. 25 mm deep Use cord outlet accessory box Cat.No 7 300 53 for external cord outlet ASTA licence Nominal plate dimensions: 86 x 86 mm DP switch
10	7 300 12	DP switch + red LED power indicator LED invisible until activated
10	7 301 10	DP switch marked "WATER HEATER"
10	7 301 12	DP switch marked "WATER HEATER" + red LED power indicator LED invisible until activated

Pack	Cat.Nos	Double pole switches 45 A - 250 V~
10	7 300 22	Conform to BS EN 60669-1 ASTA licence For flush-mounting, back box to be min. 45 mm deep Nominal plate dimensions: 86 x 86 mm DP switch
10	7 300 23	DP switch + red LED power indicator LED invisible until activated
10	7 301 22	DP switch red rocker marked "COOKER"
5	7 300 20	Nominal plate dimensions: 146 x 86 mm DP switch
5	7 300 21	DP switch + red LED power indicator LED invisible until activated
5	7 301 20	DP switch red rocker marked "COOKER"

Synergy™

telephone, data and TV sockets - white



7 300 50

7 300 57

7 300 43

Front plates: white thermoset
Terminal screws captive and backed off ready for cabling - large angled terminal entries
Compact mechanism for maximised wiring space
Supplied with faceplate screw caps

Pack	Cat.Nos	Euro module front plates
10	7 300 99	Suitable for use with standard 25 x 50 mm Euro data module inserts 1 gang - 86 x 86 mm 2 modules - aperture size 50 x 50 mm
10	7 301 00	2 gang - 86 x 146 mm 4 modules - aperture size 50 x 100 mm
10	7 300 50	Telephone sockets For flush-mounting, back box to be min. 35 mm deep Nominal plate dimensions: 86 x 86 mm UK master
10	7 300 51	UK secondary
10	7 300 54	RJ 11/RJ 12 - single
1	7 300 56	Data sockets - Cat. 6 Rapid cable connection For flush-mounting, back box to be min. 35 mm deep Nominal plate dimensions: 86 x 86 mm RJ 45 - single
1	7 300 57	RJ 45 - twin
1	7 300 43	TV sockets For DVBT, Cablecast and satellite installation UHD TV compatible Class A shielded star sockets LTE Ready (4G protected) Recommended coaxial cable: 17 VATC Star cabling (1 socket = 1 cable to antenna, splitter or multiswitch) Visual checking of the connection Meet EN 50083-4 and EN 50083-2 European directive TV: male connector (Ø9.5 mm) R: female connector (Ø9.5 mm) SAT: "F type" connector TV: 5-68 / 120-862 MHz R: 87.5-108 MHz SAT: 950-2400 MHz 2 modules For technical characteristics, see e-catalogue
1	7 300 43	Multi TV star sockets TV-R-SAT Low attenuation: < 1.5 dB
10	7 300 40	Single TV star sockets TV 9.5 mm male
1	7 300 41	TV "F" type