

Synergy™

single pole switches and dimmers - Authentic



8 330 00

8 332 02

8 334 03

8 331 51

8 333 57

Slim front plate:

BSS: Plates made of austenitic Stainless Steel - non-magnetic - grade 304 L

PSS: Plates made of Stainless Steel + rust resistance

GG: Plates made of Stainless Steel + rust resistance

Terminal screws captive and backed off ready for cabling - large angled terminal entries. Compact mechanism for maximum wiring space

Single pole plate switches 10 AX - 250 V~

Pack	Cat.Nos	
		Conform to BS EN 60669-1 For flush-mounting, back box to be min. 16 mm deep
		1 gang - 1-way switches Nominal plate dimensions: 86 x 86 mm
1	8 330 00	● Brushed stainless steel
1	8 332 00	● Polished stainless steel
1	8 334 00	● Glossy gold
		1 gang - 2-way switches Nominal plate dimensions: 86 x 86 mm
1	8 330 01	● Brushed stainless steel
1	8 332 01	● Polished stainless steel
1	8 334 01	● Glossy gold
		1 gang - intermediate switches Nominal plate dimensions: 86 x 86 mm
1	8 330 05	● Brushed stainless steel
1	8 332 05	● Polished stainless steel
1	8 334 05	● Glossy gold
		2 gang - 2-way switches Nominal plate dimensions: 86 x 86 mm
1	8 330 02	● Brushed stainless steel
1	8 332 02	● Polished stainless steel
1	8 334 02	● Glossy gold
		3 gang - 2-way switches Nominal plate dimensions: 86 x 86 mm
1	8 330 03	● Brushed stainless steel
1	8 332 03	● Polished stainless steel
1	8 334 03	● Glossy gold
		4 gang - 2-way switches Nominal plate dimensions: 86 x 146 mm
1	8 330 04	● Brushed stainless steel
1	8 332 04	● Polished stainless steel
1	8 334 04	● Glossy gold

Single pole push switches 10 A - 250 V~

Pack	Cat.Nos	
		Conform to BS EN 60669-1 For flush-mounting, back box to be min. 16 mm deep Nominal plate dimensions: 86 x 86 mm
		1 gang - 2-way push switches
1	8 330 07	● Brushed stainless steel
1	8 332 07	● Polished stainless steel
1	8 334 07	● Glossy gold

Single pole plate switches 20 AX - 250 V~

Pack	Cat.Nos	
		Conform to BS EN 60669-1 For flush-mounting, back box to be min. 16 mm deep Nominal plate dimensions: 86 x 86 mm
		1 gang - 2-way switches
1	8 331 31	● Brushed stainless steel
1	8 333 31	● Polished stainless steel
1	8 335 31	● Glossy gold

Single pole plate switches 20 AX - 250 V~ (continued)

Pack	Cat.Nos	
		2 gang - 2-way switches
1	8 331 32	● Brushed stainless steel
1	8 333 32	● Polished stainless steel
1	8 335 32	● Glossy gold
		3 gang - 2-way switches
1	8 331 33	● Brushed stainless steel
1	8 333 33	● Polished stainless steel
1	8 335 33	● Glossy gold

Push on/off rotary universal dimmers 5 W/300 W

Pack	Cat.Nos	
		1 gang Conform to IEC 60669-2-1 For flush mounting back box to be min. 40 mm deep Equipped with overvoltage and short-circuit protection Screw terminals. For all types of lamps: - dimmable LEDs: 5 W to 75 W - dimmable compact fluorescent lamps: 5 W to 75 W - halogen with ferromagnetic or electronic transformer: 5 VA to 300 VA - fluorescent tube - ballast: 5 VA to 300 VA - halogen and incandescent 230 V: 5 W to 300 W When switched on, gradually (2 seconds) lights up at the level set before last switch-off Nominal plate dimensions: 86 x 86 mm Can be associated with an active power compensator (p. 590)
1	8 331 51	● Brushed stainless steel
1	8 333 51	● Polished stainless steel
1	8 335 51	● Glossy gold

Push on/off rotary dimmers 400 W 100-240 V~ - 50/60 Hz

Pack	Cat.Nos	
		Conform to BS EN 60669-1-2 For flush-mounting, back box to be min. 25 mm deep Nominal plate dimensions: 86 x 86 mm
		1 gang - 2 way
1	8 331 56	● Brushed stainless steel
1	8 333 56	● Polished stainless steel
1	8 335 56	● Glossy gold
		2 gang - 2 way
1	8 331 57	● Brushed stainless steel
1	8 333 57	● Polished stainless steel
1	8 335 57	● Glossy gold

Push on/off rotary dimmers 1000 W 100-240 V/50-60 Hz

Pack	Cat.Nos	
		Conform to BS EN 60669-1 - For flush-mounting back box to be min. 40 mm deep - 60-1000 W (230 V) - 60-500 W(127 V) for incandescent and halogen lamps 60-600 VA (230 V) - 60-300 VA (127 V) for halogen lamps with electronic transformers 60-100 VA (230 V) - 60-500 VA (127 V) for halogen lamps with ferromagnetic transformers Nominal plate dimensions: 86 x 86 mm
		1 gang
1	8 331 50	● Brushed stainless steel
1	8 333 50	● Polished stainless steel
1	8 335 50	● Glossy gold