

## Synergy™ - cooker control units and fused connection units - Authentic



8 332 29

8 334 37









Slim front plate:

BSS: Plates made of austenitic Stainless Steel - non-magnetic - grade 304 L

PSS: Plates made of Stainless Steel + rust resistance

GG: Plates made of Stainless Steel + rust resistance

Terminal screws captive and backed off ready for cabling - large angled terminal entries. Compact mechanism for maximum wiring space

| Pack | Cat.Nos  | Cooker control units - 250 V~  |
|------|----------|--|
|      |          | Conform to BS 4177: 1992<br>For flush-mounting, back box to be min. 47 mm deep<br>Nominal plate dimensions: 86 x 146 mm  |
|      |          | <b>45 A DP switch + 13 A DP switched socket outlet with blue LED power indicator</b>   |
| 1    | 8 330 29 |  <ul style="list-style-type: none"> <li>● Brushed stainless steel</li> <li>● Polished stainless steel</li> <li>● Glossy gold</li> </ul>   |
| 1    | 8 332 29 |  |
| 1    | 8 334 29 |  |
|      |          | <b>Fused connection units 13 A - 250 V~</b>  |
|      |          | Conform to BS 1363: Part. 4<br>Front cable outlet with cord grip<br>Fuse supplied<br>Locked captive fuse carrier (padlockable)<br>For flush-mounting, back box to be min. 25 mm deep                                       |
|      |          | <b>Unswitched with cord outlet</b><br>Nominal plate dimensions: 86 x 86 mm   |
| 1    | 8 330 32 |  <ul style="list-style-type: none"> <li>● Brushed stainless steel</li> <li>● Polished stainless steel</li> <li>● Glossy gold</li> </ul> |
| 1    | 8 332 32 |  |
| 1    | 8 334 32 |  |
|      |          | <b>Unswitched without cord outlet</b><br>Nominal plate dimensions: 86 x 86 mm  |
| 1    | 8 330 30 |  <ul style="list-style-type: none"> <li>● Brushed stainless steel</li> <li>● Polished stainless steel</li> <li>● Glossy gold</li> </ul> |
| 1    | 8 332 30 |  |
| 1    | 8 334 30 |  |
|      |          | <b>Unswitched with blue LED power indicator</b><br>Nominal plate dimensions: 86 x 86 mm  |
| 1    | 8 330 31 |  <ul style="list-style-type: none"> <li>● Brushed stainless steel</li> <li>● Polished stainless steel</li> <li>● Glossy gold</li> </ul> |
| 1    | 8 332 31 |  |
| 1    | 8 334 31 |  |
|      |          | <b>Unswitched with blue LED power indicator + cord outlet</b><br>Nominal plate dimensions: 86 x 86 mm  |
| 1    | 8 330 33 |  <ul style="list-style-type: none"> <li>● Brushed stainless steel</li> <li>● Polished stainless steel</li> <li>● Glossy gold</li> </ul> |
| 1    | 8 332 33 |  |
| 1    | 8 334 33 |  |
|      |          | <b>DP switched without cord outlet</b><br>Nominal plate dimensions: 86 x 86 mm   |
| 1    | 8 330 34 |  <ul style="list-style-type: none"> <li>● Brushed stainless steel</li> <li>● Polished stainless steel</li> <li>● Glossy gold</li> </ul> |
| 1    | 8 332 34 |  |
| 1    | 8 334 34 |  |
|      |          | <b>DP switched with blue LED power indicator</b><br>Nominal plate dimensions: 86 x 86 mm   |
| 1    | 8 330 35 |  <ul style="list-style-type: none"> <li>● Brushed stainless steel</li> <li>● Polished stainless steel</li> <li>● Glossy gold</li> </ul> |
| 1    | 8 332 35 |  |
| 1    | 8 334 35 |  |
|      |          | <b>DP switched with blue LED power indicator + cord outlet</b><br>Nominal plate dimensions: 86 x 86 mm   |
| 1    | 8 330 37 |  <ul style="list-style-type: none"> <li>● Brushed stainless steel</li> <li>● Polished stainless steel</li> <li>● Glossy gold</li> </ul> |
| 1    | 8 332 37 |  |
| 1    | 8 334 37 |  |

## Synergy™ - shaver sockets, cable outlets, blanking plates and cord outlets - Authentic



8 332 90

8 330 19

8 334 95







Slim front plates:

BSS: Plates made of austenitic Stainless Steel - non-magnetic - grade 304 L

PSS: Plates made of Stainless Steel + rust resistance

GG: Plates made of Stainless Steel + rust resistance

Terminal screws captive and backed off ready for cabling - large angled terminal entries. Compact mechanism for maximum wiring space

| Pack | Cat.Nos  | Shaver sockets  |
|------|----------|---|
|      |          | Conform to BS EN 61558-2-5<br>Suitable for use with European, British and Australian 2 pin plugs<br>Rating: 20 VA<br>IP 24<br>Screwless live and neutral terminals<br>For flush-mounting, back box to be min. 45 mm deep<br>Nominal plate dimensions: 146 x 86 mm |
|      |          | <b>230/120 V~ - 50/60 Hz</b>  |
| 1    | 8 330 90 |  <ul style="list-style-type: none"> <li>● Brushed stainless steel</li> <li>● Polished stainless steel</li> <li>● Glossy gold</li> </ul>                                       |
| 1    | 8 332 90 |   |
| 1    | 8 334 90 |   |
|      |          | <b>Cable outlets</b>  |
|      |          | Conform to BS 5733<br>Fitted clamp and outlet membrane<br>With terminal block<br>Nominal plate dimensions: 86 x 86 mm   |
|      |          | <b>20 A - 250 V~</b>  |
| 1    | 8 330 19 |  <ul style="list-style-type: none"> <li>● Brushed stainless steel</li> <li>● Polished stainless steel</li> <li>● Glossy gold</li> </ul>                                       |
| 1    | 8 332 19 |   |
| 1    | 8 334 19 |   |
|      |          | <b>45 A - 250 V~</b>  |
| 1    | 8 330 26 |  <ul style="list-style-type: none"> <li>● Brushed stainless steel</li> <li>● Polished stainless steel</li> <li>● Glossy gold</li> </ul>                                       |
| 1    | 8 332 26 |   |
| 1    | 8 334 26 |   |
|      |          | <b>Blanking plates</b>  |
|      |          | <b>1 gang</b><br>Nominal plate dimensions: 86 x 86 mm   |
| 1    | 8 330 95 |  <ul style="list-style-type: none"> <li>● Brushed stainless steel</li> <li>● Polished stainless steel</li> <li>● Glossy gold</li> </ul>                                       |
| 1    | 8 332 95 |   |
| 1    | 8 334 95 |   |
|      |          | <b>2 gang</b><br>Nominal plate dimensions: 86 x 146 mm  |
| 1    | 8 330 96 |  <ul style="list-style-type: none"> <li>● Brushed stainless steel</li> <li>● Polished stainless steel</li> <li>● Glossy gold</li> </ul>                                       |
| 1    | 8 332 96 |   |
| 1    | 8 334 96 |   |
|      |          | <b>Cord outlets</b>   |
|      |          | <b>1 gang</b><br>Nominal plate dimensions: 86 x 86 mm   |
| 1    | 8 330 52 |  <ul style="list-style-type: none"> <li>● Brushed stainless steel</li> <li>● Polished stainless steel</li> <li>● Glossy gold</li> </ul>                                       |
| 1    | 8 332 52 |   |
| 1    | 8 334 52 |   |