

## Synergy™ - telephone, data sockets and television sockets - Sleek Design



8 320 50

8 324 57

8 322 41

Sleek design

BSS: Plates made of austenitic Stainless Steel - non-magnetic - grade 304 L

PSS: Plates made of Stainless Steel + rust resistance

GG: Plates made of Stainless Steel + rust resistance

Terminal screws captive and backed off ready for cabling - large angled terminal entries

Compact mechanism for maximum wiring space

Pack	Cat.Nos	Telephone sockets
		For flush-mounting, back box to be min. 35 mm deep Nominal plate dimensions: 86 x 86 mm
		<b>UK master</b>
1	8 320 50	● Brushed stainless steel
1	8 322 50	● Polished stainless steel
1	8 324 50	● Glossy gold
		<b>UK secondary</b>
1	8 320 51	● Brushed stainless steel
1	8 322 51	● Polished stainless steel
1	8 324 51	● Glossy gold
		<b>RJ 11 / RJ 12 - single</b>
1	8 320 54	● Brushed stainless steel
1	8 322 54	● Polished stainless steel
1	8 324 54	● Glossy gold

Pack	Cat.Nos	Data sockets Cat. 6
		Rapid cable connection For flush-mounting, back box to be min. 35 mm deep Nominal plate dimensions: 86 x 86 mm
		<b>RJ 45 - single</b>
1	8 320 56	● Brushed stainless steel
1	8 322 56	● Polished stainless steel
1	8 324 56	● Glossy gold
		<b>RJ 45 - twin</b>
1	8 320 57	● Brushed stainless steel
1	8 322 57	● Polished stainless steel
1	8 324 57	● Glossy gold

Pack	Cat.Nos	Television sockets
		For flush-mounting, back box to be min. 35 mm deep Screened Nominal plate dimensions: 86 x 86 mm
		<b>TV sockets - single male</b>
1	8 320 40	● Brushed stainless steel
1	8 322 40	● Polished stainless steel
1	8 324 40	● Glossy gold
		<b>SAT sockets - single "F" type</b>
1	8 320 41	● Brushed stainless steel
1	8 322 41	● Polished stainless steel
1	8 324 41	● Glossy gold
		<b>TV-R-SAT sockets - "F" type</b>
1	8 320 43	● Brushed stainless steel
1	8 322 43	● Polished stainless steel
1	8 324 43	● Glossy gold

## Synergy™ - cooker control units, fused connection units and cable outlets - Sleek Design



8 320 32

8 322 37

8 324 19

Sleek design

BSS: Plates made of austenitic Stainless Steel - non-magnetic - grade 304 L

PSS: Plates made of Stainless Steel + rust resistance

GG: Plates made of Stainless Steel + rust resistance

Terminal screws captive and backed off ready for cabling - large angled terminal entries

Compact mechanism for maximum wiring space

Pack	Cat.Nos	Cooker control units - 250 V~
		Conform to BS 4177: 1992. For flush-mounting, back box to be min 47 mm deep Nominal plate dimensions: 86 x 146 mm
		<b>45 A DP switch + 13 A DP switched socket outlet - with blue LED power indicator</b>
1	8 320 29	● Brushed stainless steel
1	8 322 29	● Polished stainless steel
1	8 324 29	● Glossy gold

Pack	Cat.Nos	Fused connection units unswitched 13 A - 250 V~
		Conform to BS 1363: Part. 4. Front cable outlet with cord grip. Fuses supplied. Locked captive fuse carrier (padlockable). For flush-mounting, back box to be min. 35 mm deep. Supplied with 1 gang side extension (3 mm thick) in case of extra wiring space needed Nominal plate dimensions: 86 x 86 mm
		<b>Unswitched - with cord outlet</b>
1	8 320 32	● Brushed stainless steel
1	8 322 32	● Polished stainless steel
1	8 324 32	● Glossy gold

Pack	Cat.Nos	Fused connection units switched 13 A - 250 V~
		Conform to BS 1363: Part. 4. Front cable outlet with cord grip. Fuses supplied. Locked captive fuse carrier (padlockable). For flush-mounting, back box to be min. 35 mm deep. Supplied with 1 gang side extension (3 mm thick) in case of extra wiring space needed Nominal plate dimensions: 86 x 86 mm
		<b>DP switched - with blue LED power indicator - without cord outlet</b>
1	8 320 35	● Brushed stainless steel
1	8 322 35	● Polished stainless steel
1	8 324 35	● Glossy gold
		<b>DP switched - with blue LED power indicator + cord outlet</b>
1	8 320 37	● Brushed stainless steel
1	8 322 37	● Polished stainless steel
1	8 324 37	● Glossy gold

Pack	Cat.Nos	Cable outlets
		Conform to BS 5733. Fitted with clamp and outlet membrane. With terminal block Nominal plate dimensions: 86 x 86 mm
		<b>20 A - 250 V~</b>
1	8 320 19	● Brushed stainless steel
1	8 322 19	● Polished stainless steel
1	8 324 19	● Glossy gold
		<b>45 A - 250 V~</b>
1	8 320 26	● Anthracite grey colour (plastic)