

# Plexo™ mechanisms

prewired socket outlets, data, TV sockets and adaptors - IP 55



Mechanisms supplied with cover plate  
Installation with surface-mounting boxes or flush-mounting support frames (p. 607)

Pack	Cat.Nos		Pack	Cat.Nos	
5	0 695 76	<b>Prewired German standard socket outlets 16 A - 250 V~</b> Automatic terminals One piece mechanism, only one connection required For two or three gang surface-mounting boxes or flush-mounting supports <b>2 x 2P+E horizontal</b> ● Grey	10	0 695 80	<b>Adaptors for 2-module Arteor/Mosaic mechanisms</b> Can be equipped with any 2-module Arteor functions (except specific mechanisms with depth > 18 mm) in order to obtain an IP 55 wiring device <b>Adaptor with smoked polycarbonate flap</b> ○ Grey/white
5	0 695 77	<b>2 x 2P+E vertical</b> ● Grey	1	0 695 79	<b>Adaptor with smoked polycarbonate flap lockable</b> Lockable with special tool Cat.No 0 919 45 ○ Grey/white
5	0 695 59	<b>RJ 45 data sockets</b> IP 55 with closed shutter IK 07 <b>Cat. 6<sub>A</sub> STP</b> ● Grey	1	0 695 82	<b>Adaptor without flap - IP 20</b> ○ Grey/white
5	0 695 69	<b>Cat. 6 FTP</b> ● Grey	1	6 806 33	<b>Adaptors for 3-module Arteor/Mosaic mechanisms</b> Weatherproof IP 55 with membrane Allows operations of switches without opening cover maintaining IP 55 rating ● Grey ○ White
1	0 695 61	<b>Cat. 6 UTP</b> ● Grey	1	6 806 32	
1	0 695 57	<b>Cat. 5e FTP</b> ● Grey	1	0 919 45	<b>Accessories</b> Special tool for adaptor Cat.No 0 695 79
1	0 695 56	<b>Cat. 5e UTP</b> ● Grey	100	0 849 00	Standard claws Long claws
1	0 707 24	<b>TV-R-SAT socket</b> For DVBT, Cablecast and satellite installation UHD TV compatible Class A shielded star socket LTE Ready (4G protected) Recommended coaxial cable: 17 VATC Star cabling (1 socket = 1 cable antenna, splitter or multiswitch) Visual check of the connection Meets EN 50083-4 and EN 50083-2 European directive ○ White antimicrobial <sup>(1)</sup>	50	0 849 01	

1: Contains a silver compound to prevent the growth of bacteria on the surface