

Plexo™ 66 complete flush-mounting

IP 66 - IK 08



6 845 53



6 845 56



6 845 70

White RAL 9010

Polypropylene/ABS housing

Supplied without back boxes, can mount directly on to standard metal flush boxes

Stainless steel captive terminal screws supplied in backed-off position

Supplied with flush-mounting gasket

Supplied without lamps

Pack	Cat.Nos	20 A - 250 V~ switches
1	6 845 53	Flush-mounting gasket is not required when fitting these mechanisms on to back boxes Cat.Nos 6 845 89/90/91 1 gang 2 way switch - SP
1	6 845 54	2 gang 2 way SP
1	6 845 56	1 gang 1 way DP + indicator
1	6 845 60	6 A - 250 V~ push-button 1 gang 2 way SP retractive switch
1	6 845 70	13 A - 250 V~ socket outlet 1 gang unswitched
1	6 845 85	Arteor/Mosaic adaptor 2 modules with opaque lid

Plexo™ 66 complete surface-mounting

IP 66 - IK 08



6 846 19



0 904 67

Grey RAL 7016/TO 29

Supplied with ISO 20 membrane glands and caps for rear cabling

For top or down cabling, plastic cable glands (p. 315) have to be used

Stainless steel captive terminal screws supplied in backed-off position

Pack	Cat.Nos	20 A - 250 V~ switches
1	6 846 03	Fitted with rear gasket with groove to deposit silicone 1 gang Two-way switch - SP
1	6 846 02	1 gang One way switch - DP
1	6 846 04	2 gang Two-way switch - SP
1	6 846 11	6 A - 250 V~ push-buttons 1 gang Two-way switch - SP with "Bell"
1	6 846 45	13 A - 250 V~ fused spur unit Fitted with rear gasket with groove to deposit silicone 1 gang - DP switched
1	6 846 22	13 A - 250 V~ socket outlets Fitted with rear gasket with groove to deposit silicone 1 gang Switched socket with opaque lid
1	6 846 20	1 gang Unswitched socket with opaque lid
1	6 846 19	1 gang unswitched Accepts moulded plugs with side outlet
1	6 846 28	2 gang unswitched
1	0 904 67	RJ 45 socket Cat.6 - FTP
1	6 846 36	Arteor/Mosaic adaptors 2 module adaptor - semi-transparent lid
1	6 846 38	3 module adaptor - semi-transparent lid