



Pack	Cat.Nos	Product Name
10	0 601 95	Ceiling roses Terminals: 5 x 0.75 mm ² , 3 x 1.5 mm ² , 2 x 2.5 mm ² , 2 x 4 mm ² Strong load grips support: up to 5 kg With screw connection 3 pin ceiling rose - 250 V - 6A
20	0 601 96	With plug-in connection 3-pin
20	0 601 98	4 pin white. Fire resistant UL94Vo
20	0 601 97	4 pin red. Fire resistant UL 94 Vo

50	0 601 21	E 27 lampholder Insulating material - 100 W Screw connection Threaded base - single bushing 10 mm connector With retaining screw 4 A - 250 V~
----	----------	--

10	0 601 30	Lampholders for public lighting Porcelain - white Base retaining clip, protective skirt 4 A - 250 V~ E 27 lampholder
10	0 601 80	Base retaining clip - 16 A max. One piece unit 16 A - 750 V~ E 40 lampholder

20	0 401 87	Cord switches Fluorescent Easy connection by cutting the 2 wires Double pole White spotted
20	0 401 92	Coloured Easy connection by cutting the 2 wires Double pole White
20	0 401 93	Old gold, old gold rocker
20	0 401 94	Black

10	0 401 75	Door contact switch Normally closed contactor complete with roller actuator Automatically illuminates cupboards upon opening of the door Single pole 2 A - 250 V
----	----------	--



Pack	Cat.Nos	Product Name
1	SL189800	Led shaverlights - IP 44 Lifetime: 40,000 hours Color temperature: 4000 K CRI > 80 Opal diffuser for better distribution of the luminous flux Screwless connection terminals 500 lm Dimensions: 5.6 cm x 36 cm ON/OFF
1	SL189801	With sensitive switch
1	SL189810	800 lm Dimensions: 6.13 cm x 50 cm ON/OFF
1	SL189820	With sensitive switch
1	SL189850	With sensitive switch + 2P French standard socket
1	190817	Fluorescent shaverlights - French standard IP 24 - IK 04 - class II 2G7 - 11 W - 900 lm Unswitched
1	190827	Switched
1	289899	Halogen tube 50 W, for halogen shaverlights maintenance