










Motion and Lighting Management sensors for 1 circuit

selection chart

MOTION SENSORS			
AREAS WITHOUT NATURAL LIGHT	INSTALLATION		
	Ceiling** 	Surface-mounting ⁽²⁾	Wall 
			Flush-mounting ⁽¹⁾
		Mosaic	Arteor
PASSAGE AREAS			
Hall / lobby Stairways / hallways Storage areas / technical areas	 0 489 41 ⁽¹⁾ /44*/48 ⁽¹⁾	 0 489 42/45*	 With neutral: 0 784 54 Without neutral: 0 784 58 ⁽⁴⁾ Without neutral, for time-lag switch: 0 784 57  With neutral: 5 740 47 Without neutral: 5 740 09 ⁽⁴⁾
OUTDOOR AND HUMID AREAS			
IP 55 Internal/external parking lot Internal entrance areas	 0 697 40 / 0 697 80	 0 489 43/46* Fixed head  0 697 40 Directional head	-

1: Surface-mounting box option - 2: angle mounting option - 3: 1 lighting output + 1 fan output - 4: Retro-fit dedicated solution - *Blister - ** Except for Cat.No 0 489 58 (batten-mounted)