

Connectivity and housing selection tables

configure your system (continued)



RJ 45 PATCH AND USER CORDS				LCS ³		
				LCS ³ cat. 8	LCS ² cat. 6 _A	LCS ² cat. 6
	S/FTP	Impedance 100 Ω	0.5 m	-	● 0 518 16	-
			1 m	-	● 0 517 80	-
			2 m	-	● 0 517 81	-
			3 m	-	● 0 517 82	-
			5 m	-	● 0 517 83	-
	SF/UTP	Impedance 100 Ω	0.5 m	-	-	● 0 517 52
			1 m	-	-	● 0 517 53
			2 m	-	-	● 0 517 54
			3 m	-	-	● 0 517 55
			5 m	-	-	● 0 518 15
	F/UTP	Impedance 100 Ω	1 m	-	-	● 0 517 62
			2 m	-	-	● 0 517 63
			3 m	-	-	● 0 517 64
			5 m	-	-	● 0 517 65
			U/UTP	Impedance 100 Ω	0.5 m	-
	1 m	-	-		● 0 517 72	
	2 m	-	-		● 0 517 73	
	3 m	-	-		● 0 517 74	
	5 m	-	-		● 0 517 75	
				15 m	-	-
			20 m	-	-	● 0 515 12
COPPER CABLES (305 M OR 500 M DRUMS)						
	S/FTP	4 pairs	500 m	0 337 88	● 0 327 77	-
	SF/UTP	4 pairs	500 m	-	-	● 0 327 57
	F/UTP	4 pairs	305 m	-	-	● 0 328 56
			500 m	0 337 86	● 0 327 78	● 0 327 56
	F/FTP	4 pairs	500 m	-	● 0 328 78	● 0 327 76
			2 x 4 pairs	500 m	-	● 0 327 99
			500 m	-	● 0 327 98	-
LCS³ FIBRE OPTIC PATCH PANELS				OS 2 (UPC) single-mode 9/125 µm	OM 4 multimode 50/125 µm	OM 3 multimode 50/125 µm
	SC/SC duplex cords	1 m	0 326 00	0 326 30	0 326 09	
		2 m	0 326 01	0 326 31	0 326 10	
		3 m	0 326 02	0 326 32	0 326 11	
	SC/LC duplex cords	1 m	0 326 03	-	0 326 12	
		2 m	0 326 04	-	0 326 13	
		3 m	0 326 05	-	0 326 14	
	LC/LC duplex cords	0.5 m	0 326 28	0 326 33	-	
		1 m	0 326 06	0 326 34	0 326 15	
		2 m	0 326 07	0 326 35	0 326 16	
		3 m	0 326 08	0 326 36	0 326 17	
		5 m	0 326 29	0 326 37	-	
	LC/LC Uniboot duplex cords reversible polarity	1 m	0 326 86	0 326 95	-	
		2 m	0 326 87	0 326 96	-	
		3 m	0 326 88	0 326 97	-	
		5 m	0 326 89	0 326 98	-	
		10 m	0 326 92	0 326 99	-	
LCS³ FIBRE OPTIC CABLES (DRUMS)						
	Interior/exterior	4 fibre	Loose	0 325 02	0 325 43	0 325 37
		8 fibre	Loose	0 325 03	0 325 44	0 325 38
		6 fibre	Loose	0 325 12	-	-
			Tightened	-	0 326 65/66	0 325 10
		12 fibre	Loose	0 325 14	0 325 45	0 325 39
			Tightened	0 325 50	0 326 67	0 325 11
		24 fibre	Loose	0 325 51	-	0 325 53
			Tightened	-	0 326 68	0 325 52
	Exterior, steel rodent guard, free	4 fibre optics	0 325 23	0 325 46	-	
		8 fibre optics	0 325 24	0 325 47	0 325 40	
		6 Loose fibre optics	0 325 13	-	-	
		12 fibre optics	0 325 15	0 325 48	0 325 41	
			24 fibre optics	0 325 25	-	0 325 42