

## Connectivity and housing selection tables

configure your system (continued)

LCS <sup>3</sup> 1 U 19" SINGLE PHASE PDU - POWER DISTRIBUTION UNITS (p. 771)			Connection on 6 mm <sup>2</sup> terminal block		3 m cord on 16 A plug	
	6 outlets	German Standard	-	-	6 468 06	
	9 outlets	German Standard	-	-	6 468 12	
	8 outlets	British Standard	-	-	6 468 13	
	6 outlets	French Standard	-	-	6 468 05	
	9 outlets	French Standard	-	-	6 468 10	
	9 outlets-red	French Standard	-	-	6 468 11	
	10 outlets	C13 - IEC 60320	6 468 14	-	-	
	12 outlets	C13 - IEC 60320	-	-	6 468 15	
	8 outlets	C13 (6) and C19 (2) - IEC 60320	6 468 09	-	-	
6 outlets	C13 - IEC 60320	6 468 07	-	-		
LCS <sup>3</sup> 1 U 10" SINGLE PHASE PDU - POWER DISTRIBUTION UNITS (p. 771)			Connection on 6 mm <sup>2</sup> terminal block	1 m cord on 16 A plug	With Ammeter	With Surge protection
	4 outlets	German Standard	-	6 468 01	-	-
	4 outlets	French Standard	-	6 468 00	-	-
LCS <sup>3</sup> 1 U 19" SINGLE PHASE PDU - WITH POWER/LUMINOUS INDICATORS (p. 771)			Power Indicator		Luminous Switch	
	9 outlets	German Standard	6 468 21	-	-	
	8 outlets	German Standard	-	-	6 468 23	
	6 outlets	British Standard	-	-	6 468 24	
	9 outlets	French Standard	6 468 20	-	-	
	8 outlets	French Standard	-	-	6 468 22	
LCS <sup>3</sup> 1 U 19" SINGLE PHASE PDU - POWER DISTRIBUTION UNITS (p. 772)			With MCB	With 30 mA RCCB	With Surge protection	With Ammeter
	6 outlets	German Standard	6 468 31	-	6 468 36	6 468 41
	9 outlets	German Standard	<b>N</b> 6 468 32	-	-	-
	6 outlets	French Standard	6 468 30	6 468 33	6 468 35	-
LCS <sup>3</sup> METERED PDU - POWER DISTRIBUTION UNITS (p. 773) <b>N</b>			19"		Vertical 0U	
	12 outlets	C13 with 3 m cord on C20 plug	6 460 10	-	-	
	16 outlets	C13 (12) and C19 (4) with 3 m cord on IEC60309 32 A 2P+E plug	6 460 11	-	-	
	16 outlets	C13 (18) and C19 (4) with 3 m cord on IEC60309 16 A 2P+E plug	-	-	6 460 12	
	42 outlets	C13 (36) and C19 (6) with 3 m cord on IEC60309 32 A 2P+E plug	-	-	6 460 13	
	42 outlets	C13 (36) and C19 (6) with 3 m cord on 3-phase IEC60309 16 A 3P+N+E plug	-	-	6 460 14	
	42 outlets	C13 (30) and C19 (12) with 3 m cord on 3-phase IEC60309 32 A 3P+N+E plug	-	-	6 460 15	