

Legrand cabling system LCS³ category 6A

RJ 45 sockets - Mosaic™ Programme



Can be integrated in all supports (p. 845-873)
 Mechanisms to be equipped with support frames (p. 906) and plates (p. 904-905)
 With LCS³ connector with fast connection thanks to integrated crimping take AWG 22 single-core cables up to AWG 26 and AWG multicore cables
 Contacts marked with dual colour code and wiring schemes T568 A and T 568 B
 Conform to standards ISO/IEC 11801 Ed. 3.0, amendment 2, EN 50173-1 and TIA/EIA 568 C

Pack	Cat.Nos	Mosaic Programme RJ 45 sockets cat. 6A	Pack	Cat.Nos	Keystone RJ 45 sockets cat. 6A
		STP - 1 module 360° metal shielding	10	0 331 54	STP socket - metal shielding 360° with fast connection thanks to integrated crimping
10	0 765 73	○ White	10	0 331 55	UTP socket - with fast connection thanks to integrated crimping
10	0 765 84	○ White antimicrobial			
10	0 794 73	● Aluminium			
		STP - 2 modules 360° metal shielding			Surface-mounting 1 or 2 ports box
10	0 765 76	○ White	1	6 327 79	For keystone connectors
10	0 794 76	● Aluminium			Provides a solution for the integration of a keystone in surface-mounting installations
10	0 765 24	○ White with green shutter			Can be fixed on table or in association with mini-trunking
10	0 765 25	○ White with orange shutter			
10	0 765 08	○ White			
		STP with controlled access - 2 modules 360° metal shielding Supplied with 2 keys for 5 sockets			
5	0 765 99	○ White with red shutter			
		UTP - 1 module			
10	0 765 71	○ White			
10	0 794 71	● Aluminium			
10	0 765 26	○ White with green shutter			
10	0 765 27	○ White with orange shutter			
		UTP - 2 modules			
10	0 765 74	○ White			
10	0 794 74	● Aluminium			
		UTP with controlled access - 2 modules Supplied with 2 keys for 5 sockets			
5	0 765 90	○ White with red shutter			
10	0 765 09	○ White			