

## Legrand cabling system LCS<sup>3</sup> Enclosures - accessories for wall mounting enclosures



4 461 95

Pack	Cat.Nos	19" profiles
		Can be used when fitting shelves of equipment is desired (with attachments front and back) Delivered in sets of 2
1	4 461 95	Height: 6 U
1	4 461 96	Height: 9 U
1	4 461 97	Height: 12 U
1	4 461 98	Height: 15 U
1	4 461 99	Height: 21 U
		<b>Glazed doors</b>
		Glass panel door with clear glass for the MWE enclosure Width: 600 mm
1	9 004 73	Glass door 6 U
1	9 004 74	Glass door 9 U
1	9 004 75	Glass door 12 U
1	9 004 76	Glass door 15 U
1	9 004 77	Glass door 21 U

## Legrand cabling system LCS<sup>3</sup> Enclosures 19" accessories



0 465 22



0 465 23



0 465 29



0 465 32



4 462 10

Pack	Cat.Nos	19" cable feedthrough panels
		Ensure the correct arrangement and routing of the patch cords. RAL 9005 (black)
		<b>Metal, 2 axes, Quick-Fix</b> Horizontal feedthrough passage. With cable rings plastic cable guide with controlled radius for optimum cord protection (compliance with the bending radius) Quick installation without screws
1	0 465 22	1 U
1	0 465 23	2 U
		<b>Plastic with brush, direct clipping</b>
1	0 465 28	1 U
1	0 465 29	2 U
		<b>Metal with brush, Quick-Fix</b> Quick installation without screws
1	0 465 30	1 U
1	0 465 31	2 U
		<b>1 U front panels</b> Set of 25 front panels for sealing off the 19" area so that it is airtight To be mounted between the 19" profiles No materials are needed for securing the front panel Air tight accessories enable energy savings by preventing air leakage Plastic RAL 9005 (black)
1	4 462 10	
		<b>19" blanking plates</b> RAL 9005 (black)
		<b>Plastic, direct clipping</b>
1	0 465 32	1 U
1	0 465 33	2 U
		<b>Metal, Quick-Fix</b> Quick installation without screws
1	0 465 38	1 U
1	0 465 39	2 U
1	0 465 40	3 U
		<b>19" lighting kit</b>
1	0 464 91	1 U 19" metal panel equipped with a LED lighting kit with switch Quick installation without screws 230 V~

