

Legrand cabling system LCS³ Enclosures

19" accessories (continued)



0 465 01



0 465 22



0 465 06



0 465 29

Pack	Cat.Nos	Fixed shelves
		For 19" cabinets and server cabinets, Bati racks and Altis cabinets Quick installation without screws. RAL 9005 (black)
		Suspended installation on 2 x 19" risers
		Height 2 U. Maximum load 15 kg
1	0 465 00	Depth 115 mm
1	0 465 01	Depth 200 mm
1	0 465 02	Depth 360 mm
		Installation on 4 x 19" risers
		Height 1 U. Maximum load 50 kg
1	0 465 05	Shelf depth 425 mm
1	0 465 06	For depth 600 mm
1	0 465 07	Shelf depth 625 mm
1	0 465 07	For depth 800 mm
1	0 465 07	Shelf depth 825 mm
1	0 465 07	For depth 1000 mm
		Telescopic shelves
		For 19" cabinets and server cabinets, Bati racks and Altis cabinets Quick installation on 4 x 19" risers
		Height 1 U. Maximum load: 50 kg. RAL 9005 (black)
1	0 465 08	Shelf depth 425 mm
1	0 465 09	For depth 600 mm
1	0 465 09	Shelf depth 625 mm
1	0 465 10	For depth 800 mm
1	0 465 10	Shelf depth 825 mm
1	0 465 10	For depth 1000 mm
		Heavy duty shelves
		Maximum load: 100 kg
		Fastening to the 4 x 19" risers using screws
		RAL 9005 black
1	0 465 17	Fixed shelf, depth 820 mm, 1 U
1	0 465 17	For cabinets depth 1000 mm
1	0 465 18	and server cabinets
1	0 465 18	Telescopic shelf, depth 820 mm, 2 U
1	0 465 18	For server cabinets
		Keyboard shelf
		For 19" cabinets and server cabinets, Bati racks and Altis cabinets
		For depth 800 mm and 1000 mm
		Fastening to the 4 x 19" risers
		using screws
		Maximum load: 50 kg. RAL 9005 black
		Can accept:
		- a computer screen
		- a keyboard on retractable support
		- a mouse on a sliding shelf with built-in pad mouse
		or CD housing
		Set of 2 fixed guide rails
		For 19" cabinets and server cabinets, racks and Altis cabinets
		Installation on 4 x 19" risers
		Maximum load: 50 kg
1	0 465 11	For depth 600 mm
1	0 465 12	For depth 800 mm
1	0 465 13	For depth 1000 mm

Pack	Cat.Nos	Temperature management				
		1 U ventilation drawers				
		For internal air circulation. Fix on 2 x 19" uprights				
		ON/OFF switch. Supplied with power supply cord				
		230V~				
		Black RAL 9005				
1	0 464 89	Drawer with 2 fans				
1	0 464 90	Drawer with 4 fans				
1	0 464 90	Depth 150 mm				
1	0 464 90	Depth 300 mm				
		Thermostat				
		Adjustable from 5 to 60 °C, 230 V~, 50/60 Hz				
		NC contact (5 A) and NO contact (10 A)				
		Magnet fastening				
		Fixing screws				
1	0 364 54	Set of 50 cage nuts, 50 plastic washers and 50 x M6 screws				
1	0 364 54	With 9.5 mm cage nuts				
		Self-adhesive document holders				
		Open - RAL 7035				
		Ext. dimensions				
		Int. dimensions				
		Height (mm)	Width (mm)	Height (mm)	Width (mm)	Depth (mm)
1	0 365 80	235	340	200	310	18
1	0 365 81	165	260	130	230	18
		Closed - RAL 7035				
		Rigid plastic - IP 50				
		Int. dimensions: 324 x 120 x 18 mm				
		Transparent				
		Soft plastic, A4 - 305 x 220 mm				