

Linkeo 19" freestanding cabinets

cabinets and equipment (continued)



6 465 06





6 465 01



6 465 20


Linkeo fixed shelves

Pack	Cat.Nos	Black RAL 9005
1	6 465 01	Screw fixing on 2 x 19" uprights Height 2 U. Max. load: 15 kg Shelf depth 200 mm
	6 465 02	Shelf depth 360 mm
1	6 465 05	Screw fixing on 4 x 19" uprights Height 1 U Max. load: 50 kg Shelf depth 425
	6 465 06	For depth 600 mm Shelf depth 625
	6 465 07	For depth 800 mm Shelf depth 825
	6 465 07	For depth 1000 mm



Linkeo telescopic shelves

1	6 465 08	Screw fixing on 4 x 19" uprights. Height 1 U Max. load: 30 kg. Black RAL 9005 Shelf depth 425
	6 465 09	For depth 600 mm Shelf depth 625
	6 465 10	For depth 800 mm Shelf depth 825 For depth 1000 mm



19" management panels

1	6 465 20	Fitted with cable guide rings 1 U
1	6 465 21	2 U

Linkeo 19" freestanding cabinets

Flatpack solution

- Easy to carry
- Easy to store
- Easy to handle
- Easy to mount:
 - 16 minutes / 1 person
 - dedicated installation sheet

High protection packaging (stackable)

Nota:

- cabinets delivered flatpack are exactly the same as the mounted ones. The only difference is the packaging.



Customization

1 Choose the size

Capacity	24 U	33 U	42 U	47 U
Width	600 or 800 mm			
Depth	600, 800 or 1000 mm			

2 Choose the color

- Anthracite grey (RAL 7016) or light grey (RAL 7035)

3 Choose the openings



Front and rear options

Doors

- screen-printed glass
- microperforated metal
- solid metal
- in single or double version

With or without side panels

4 Choose the equipment to mount at the factory

- cable managers
- fans
- plinths/casters
- shelves
- copper and fiber patch panels