

Linkeo 19" and 10" wall-mounting cabinets



6 462 62



6 462 21



6 462 30



0 335 92



6 468 01



0 462 23

IP 20 - IK 08

Equipped with :

- 1 reversible door made of screen-printed safety glass and with integrated lock
- 2 x 19" uprights with U marking and adjustable in depth
- 3 pre-cut cable entries (top, bottom and rear)
- 1 brush for a cable entry
- top perforations for natural ventilation
- panels with automatic grounding (ready assembled version)
- supplied with earthing kit (flatpack version)

Anthracite grey RAL 7016

Pack	Cat.Nos		Linkeo fix 19" cabinets			
	N		Fix side panels			
			Delivered ready-assembled			
	Depth 450 mm	Depth 600 mm	Capacity	Height (mm)	Width (mm)	Loading capacity (kg)
1	6 462 00	6 462 10	6 U	358	600	18
1	6 462 01	6 462 11	9 U	492	600	27
1	6 462 02	6 462 12	12 U	625	600	36
1	6 462 03	6 462 13	15 U	758	600	45
1	6 462 04	6 462 14	18 U	892	600	54
1	6 462 05	6 462 15	21 U	1035	600	63
	N		Removable side panels			
			For easy access at the side of the cabinet Opening with a lock (same key as the door) Delivered flatpack			
	Depth 450 mm	Depth 600 mm	Capacity	Height (mm)	Width (mm)	Loading capacity (kg)
1	6 462 50	6 462 60	6 U	358	600	18
1	6 462 51	6 462 61	9 U	471	600	27
1	6 462 52	6 462 62	12 U	604	600	36
1	6 462 53	6 462 63	15 U	738	600	45
1	6 462 54	6 462 64	18 U	871	600	54
1	6 462 55	6 462 65	21 U	1004	600	63

Pack	Cat.Nos	Equipment for 19" cabinets (continued)			
		Linkeo fixed shelves			
		Screw fixing on 2 x 19" uprights Height 2 U Max. load: 15 kg Black RAL 9005			
1	6 465 01	Shelf depth 200 mm For cabinets depth 400, 450 and 600 mm			
1	6 465 02	Shelf depth 360 mm For cabinets depth 450 and 600 mm			
		19" management panels			
1	6 465 20	1 U			
1	6 465 21	2 U			
		Linkeo 10" cabinet			
		Compact cabinet suitable for small business applications Delivered ready-assembled			
1	Depth 300 mm 6 462 30	Capacity 6 U	Height (mm) 358	Width (mm) 370	Loading capacity (kg) 18

Pack	Depth 610 mm	Linkeo pivoting 19" cabinets			
	N	Cabinet composed of : - base (wall fixing), can accept 19" PDU - pivoting body allowing free access to the rear of the cabinet to facilitate installation and maintenance. Reversible pivoting direction. Delivered ready-assembled			
		Capacity	Height (mm)	Width (mm)	Loading capacity (kg)
1	6 462 21	9 U	471	600	27
1	6 462 22	12 U	604	600	36
1	6 462 23	15 U	738	600	45
1	6 462 24	18 U	871	600	54
1	6 462 25	21 U	1004	600	63

Pack	Cat.Nos	Equipment for 10" cabinets			
		Panels and shelves			
1	0 337 99	10" patch panel - 1 U To be equipped with up to 12 RJ 45 connectors Supplied with screws and cage nuts			
1	0 462 23	Fixed shelf 1 U Depth 120 mm Max. load: 10 kg Black RAL 9005 Supplied with screws and cage nuts			
		10" Power Distribution Units (PDU)			
		230 V - 50/60 Hz power supply 1 U aluminium profile End cap with metallic brackets and cable holder shape Quick fixing (no screws) on 19" uprights With shutters and inclined at 55°			
1	6 468 01	4 x 2P+E outlets Black German standard 1 m power supply cord with 16 A 2P+E French/ German plug			
1	6 468 00	4 x 2P+E outlets Black French standard 1 m power supply cord with 16 A 2P+E French/German plug			
1	6 468 98	To be equipped with Mosaic wiring device modules Capacity: 8 Mosaic modules			

Pack	Cat.Nos	Equipment for 19" cabinets			
		Linkeo 19" uprights			
		Set of 2 additional 19" uprights To install at the rear of the cabinet			
1	6 462 42	12 U			
1	6 462 43	15 U			
1	6 462 44	18 U			
1	6 462 45	21 U			
		Castors			
1	6 462 48	Set of 4 castor wheels for assembly on cabinets			
		Linkeo fan kit			
1	6 462 38	Kit contains: - 2 fans - 1 thermostat - ON/OFF switch Supplied with 2.3 m cable Power supply 230 V~ - 50/60 Hz			