


# DLPlus mini-trunking 32 x 16 and 40 x 20


## profiles and finishing accessories



Cat.Nos for 32 x 16 mini-trunking

Selection chart **p. 796-797**  
 Wiring capacity chart **see e-catalogue**

Pack	Cat.Nos		Mini-trunking with cable grip
			EN 50085-2-1 approved Equipped with an integrated device for holding cables in place
			<b>Without central partition</b> Length 2.10 m
60'	32 x 16 0 308 04	40 x 20 0 300 27	Without adhesive
60'	6 489 06		With adhesive



Pack	Cat.Nos		Finishing accessories
10	32 x 16 0 312 07	40 x 20 0 312 11	End cap
10	0 333 25	0 302 81	Changeable internal-external angle
10	0 333 27	0 302 83	Changeable flat angle
20	0 336 04	0 336 06	Cover joint
10	0 333 30	0 302 08	Flat T-junction

Pack	Cat.Nos		Special frames
			Supplied with end cap and divider for separation of currents
			<b>Installation alongside the mini-trunking</b> For vertical or horizontal mounting of surface mounting wiring accessories (p. 804)
10	32 x 16 0 314 56	40 x 20 0 314 08	1 gang
5	0 314 66	0 314 18	2 gang

1: Number of metres in pack

Pack	Cat.Nos		Adaptors
			<b>Adaptors for mounting Mosaic frames at end of the mini-trunking</b>
10	32 x 16 0 316 41	40 x 20 0 316 47	For 32 x 16 and 40 x 20 mini-trunking
			<b>Adaptors for mounting Mosaic frames alongside the mini-trunking</b>
10	32 x 16 0 317 04	40 x 20 0 317 07	For Mosaic frames Cat.No 0 316 11 (p. 801)
5	0 317 05	0 317 08	For Mosaic frames Cat.Nos 0 316 13 and 0 316 21 (p. 801)
5	0 317 06	0 317 09	For Mosaic frames Cat.Nos 0 316 14 and 0 316 22 (p. 801)

Connection of luminaires **p. 801**

Junction boxes **p. 801**

Other frames for wiring accessories **p. 801**

Surface-mounting wiring accessories **p. 804**