

Flexible cover universal DLP trunking

bodies and finishing accessories

White
length: 2 m

TRUNKING			TRUNKING AND ACCESSORIES						ANGLES		
Number of compartments	Covers width (mm)	Size (mm)	Body and covers complete	Separation	Clips	Base joints ⁽¹⁾	Cover joints	End cap	Internal angle ⁽²⁾ 85 to 95°	External angle ⁽²⁾ 60 to 120°	Flat angle
FLEXIBLE COVER UNIVERSAL DLP TRUNKING - 65 mm COVER											
1		50 x 80	0 104 62	0 105 82	0 106 81	0 106 92 or 0 106 91	0 108 01	0 107 22	0 106 02	0 106 22	0 107 67
		50 x 105	0 104 24	0 105 82	0 106 81	0 106 96	0 108 01	0 107 00	0 106 05	0 106 19	0 107 86
2		50 x 150	0 104 27	0 105 82	0 106 81	0 106 92 or 0 106 91	2 x 0 108 01	0 107 03	0 106 06	0 106 35	0 107 89
3		50 x 170	0 104 67	0 105 82	0 106 82	0 106 92 or 0 106 91	2 x 0 108 00 + 0 108 01	0 107 10	0 106 50	0 106 38	0 107 98
FLEXIBLE COVER UNIVERSAL DLP TRUNKING - 85 mm COVER											
1		35 x 105	0 104 63	0 105 82	0 106 82	0 106 92 or 0 106 91	0 108 02	0 107 01	0 106 01	0 106 21	0 107 84
		50 x 105	0 104 64	0 105 82	0 106 82	0 106 92 or 0 106 91	0 108 02	0 107 02	0 106 02	0 106 22	0 107 85
2		50 x 195	0 104 70	0 105 82	0 106 82	0 106 92 or 0 106 91	2 x 0 108 02	0 107 11	0 106 06	0 106 35	0 107 92

1: 0 106 92: base joint for aligning bases, 0 106 91: base joint, attached with adhesive

2: Internal and external angles include partition junction(s) for installation with multi-compartment trunking

Flexible cover universal DLP trunking

wiring accessories supports and back boxes

SUPPORTS FOR ARTEOR AND MOSAIC		Cover width		UNIVERSAL SUPPORTS FOR 60 mm FIXING CENTRES WIRING ACCESSORIES (Valena, Niloe)		Cover width		BACK BOXES FOR BRITISH STANDARD RANGES (Belanko, Mallia, Synergy)			
		65 mm	85 mm			85 mm				Depth 25 mm	Depth 35 mm
2 modules		0 109 52	0 109 92	1 gang		0 109 13		1 gang		6 208 16	6 208 17
4 modules		0 109 54	0 109 94	2 gang		0 109 23		2 gang		6 208 26	6 208 27
6 modules		0 109 56	0 109 96	3 gang		0 109 33					
8 modules		0 109 58	0 109 98								