

Accessories for flexible cover universal DLP trunking



Pack	Cat.Nos	Accessories
1	0 306 98	Cutting accessories for trunking DLPlus cutting unit for PVC DLP For cutting all plastic bodies Avoids vibration when cutting bases and covers. Aluminium Dim.: 225 x 142 x 76 mm
10	0 304 18	Insulation accessory Base joint. Adjustable wall insulation joint, supplied in 5 m lengths Provides continuity between the trunking and the wall, in particular in internal angles
100	0 308 98	Fixing accessories for trunking For fixing all plastic profiles Wall plugs for immediate fixing No screws or nails required For mini-trunking
100	0 308 99	For mini-trunking, skirting trunking and trunking
12	0 309 49	Cartridge of Neoprene Adhesive for glue gun
200	0 308 97	DLP rapid wall plug For 10 mm min. plasterboard walls at least 20 mm away from the concrete surface For fixing DLP plastic trunking in a single operation. Used with a special tool for drill (Ø8 mm), supplied in each pack of 200 wall plugs Tensile resistance: 25 kg
100	0 106 95	Spit end cap for DLP trunking For rapid fixing of trunkings with the Spit Pulsa 700 E (use 20 mm Spit nails)
10	0 313 50	Junction boxes for DLP trunking Fitted with current separator Cable entry possible via the bottom of the box White junction boxes Dim.: 163 x 163 x 65 mm (except profile height 80 mm)
5	0 313 51	Dim.: 200 x 200 x 83 mm
5	0 313 52	Dim.: 250 x 250 x 83 mm
5	0 107 80	VDI cable management accessories To be fitted on the standard accessories (angles and junctions). For all trunking sizes except 35 x 80 trunking and in compartments with 40 mm width cover Accessory for internal angle
5	0 107 81	Accessory for external angle
5	0 107 82	Accessory for flat angle
5	0 107 83	Accessory for flat junction

Pack	Cat.Nos	Accessories
10	0 343 98	Junction and routing accessories Base for Nylobloc auto terminals For up to 3 screwless connection terminals Nylobloc auto (Cat.Nos 0 343 22/23/25/28) Direct fixing: - in top of Plexo boxes and industrial plastic cabinets ≥ 130 x 130 mm - on flat bar 12 x 2 mm - in bottom of universal and aluminium DLP trunkings (from 50 x 80 mm) Screw fixing: - in bottom of Plexo boxes ≥ 105 x 105 mm and industrial plastic cabinets - universal Fixing on rail with accessory Cat.No 0 048 11 (p. 200) Accessible test socket Marking zone with felt tip pen Cat.No 0 395 98 (p. 332)
20	0 312 10	Connection strips Connection strips with 4 x 4 mm ² terminals for junction boxes
100	0 308 81	For high current cables Base for cable ties
10	0 107 32	Flat junctions Base junctions To tap-off to a profile smaller than 50 x 105
5	0 107 33	To tap-off to an 80 mm width trunking
5	0 107 42	Accessories for separation partition Allow bottom compartment cables to pass through the separation partition in case of a flat junction For 50 mm height separation partition
5	0 107 43	For 65 mm height separation partition
5	0 107 71	Junctions for change of plane To tap-off from wall to ceiling, for example to supply power to a luminaire For cover 65 mm
5	0 107 72	For cover 85 mm
5	0 107 73	For trunking Cat.No 0 104 24
5	0 107 71+	Junctions between floor duct and trunking To tap-off to floor duct Cat.No 0 328 00 (p. 851) For cover 65 mm
5	0 106 90	For cover 85 mm
5	0 107 72+	
5	0 106 90	
5	0 106 98	Wall feedthroughs Provides a finish between the trunking and the wall For trunking 80 to 150 mm width
5	0 106 99	For trunking 195 to 220 mm width