



Universal trunking for the essentials

The DLP-S rigid cover universal trunking is recommended for traditional installation method with modular or universal supports for wiring devices



- 2 sizes supplied complete: body + cover + dividers



- Arteor mechanisms can be integrated via modular supports from 2 to 6 modules



- Non-modular British standard socket outlets like Synergy, Mallia or Belanko can be installed with the help of universal support



- The universal support for 60 mm fixing centres wiring devices allow integration of ranges like Niloe, Kaptika or Valena



DLP-S & wiring devices brochure
Available for download on
www.docexport.legrand.com

RIGID COVER TRUNKING			RIGID COVER TRUNKING			AND ACCESSORIES		FIXED ANGLES AT 90°			JUNCTION	MOUNTING WIRING ACCESSORIES				
Number of compartments	Cover width (mm)	Cross-section (mm)	Body + cover	Partition	Body joint	Cover joint	End cap	Internal angle	External angle	Flat angle	Flat junction	For 45 mm mechanisms			Universal support for British standard wiring accessories	Universal support for 60 mm fixing centres wiring devices
												2 modules	4 modules	6 modules		
		100 x 50														
			6 380 38	6 380 08	6 380 36	6 380 01	6 380 35	6 380 11	6 380 12	6 380 13	6 380 34	6 380 71	6 380 72	6 380 73	6 380 05	6 117 88
		190 x 50														
			6 380 50	6 380 08	6 380 56	6 380 01	6 380 55	6 380 51	6 380 52	6 380 53	6 380 54	6 380 71	6 380 72	6 380 73	6 380 05	6 117 88

Rigid cover DLP-S universal trunking

examples of wiring accessories

MOSAIC SOCKET OUTLETS - GERMAN STANDARD ⁽¹⁾				
		Standard	Red	Tamperproof
SCREW TERMINALS				
2P+E, 2 modules		0 776 01	0 776 11	0 776 21
2 x 2P+E, 4 modules		0 776 02	0 776 12	0 776 22
3 x 2P+E, 6 modules		0 776 03	0 776 13	0 776 23
4 x 2P+E, 8 modules		0 776 04	0 776 14	0 776 24

ARTEOR SOCKETS OUTLETS BRITISH STANDARD ⁽¹⁾			
		White	Red dedicated
2P+E, 13 A 2 modules		5 721 11	-
2 x 2P+E, switched, 13 A 3 modules		5 721 30	5 724 67

1: To be used with supports for 45 mm mechanisms Cat.Nos 6 380 71/72/73

60 MM FIXING CENTRE SOCKET OUTLETS - SCREW TERMINALS GERMAN STANDARD ⁽²⁾		
	Niloe	Kaptika
White		
2P+E	7 645 39 + 6 650 01	7 821 11
2P+E, with safety shutters	7 645 29 + 6 650 01	-
60 MM FIXING CENTRES RJ 45 SOCKETS ⁽²⁾		
	Niloe	Kaptika
White		
Cat. 5e UTP	7 645 71 + 6 650 01	7 821 24

2: To be used with universal support for 60 mm fixing centres wiring accessories Cat.No 6 117 88

BRITISH STANDARD SOCKET OUTLETS ⁽³⁾				
	Belanko		Mallia	
	1-gang	2-gang	1-gang	2-gang
White				
2P+E - 13A unswitched	6 170 40	6 170 45	2 811 10	2 811 12
2P+E - 13 A Single pole switched - 13 A	6 171 41	6 171 46	2 811 11	2 811 13
2P+E - 13 A Double pole switched - 13 A	6 170 43	6 170 48	2 811 16	2 811 17
RJ 45 DATA SOCKETS ⁽³⁾				
	Belanko		Mallia	
	Single	Twin	Single	Twin
White				
Cat. 5e UTP	6 170 90	-	2 811 61	2 811 64
Cat. 6 UTP	6 170 91	6 170 92	2 811 62	2 811 65

3: To be used with universal support for British standard wiring accessories Cat.No 6 380 05