

Standard version floor boxes for raised floor

selection chart



SOCKET MOUNTING POSITION	CAPACITY	FLOOR BOX SUPPORT KITS	LIDS & TRIMS FLOORING THICKNESS ≤ 8 mm		FINISHING PLATES (optional)		INSULATION BOXES		
Adjustable horizontal Hmin: 80 mm	12 (3 x 4) modules	0 880 20	Plastic	0 880 00	Stainless steel	0 880 15	-		
			Metal	Stainless steel	0 880 03	Stainless steel		0 880 45	
				Brass	0 880 06	Brass		0 880 48	
	18 (3 x 6) modules	0 880 21	Plastic	0 880 01	Stainless steel	0 880 16	-		
			Metal	Stainless steel	0 880 04	Stainless steel		0 880 46	
				Brass	0 880 07	Brass		0 880 49	
	24 (3 x 8) modules	0 880 22	Plastic	0 880 02	Stainless steel	0 880 17	-		
			Metal	Stainless steel	0 880 05	Stainless steel		0 880 47	
				Brass	0 880 08	Brass		0 880 50	
	Vertical Hmin: 83 mm	8 (2 x 4) modules	0 880 23	Plastic	0 880 00	Stainless steel	0 880 15	0 880 26	
				Metal	Stainless steel	0 880 03	Stainless steel		0 880 45
					Brass	0 880 06	Brass		0 880 48
12 (2 x 6) modules		0 880 24	Plastic	0 880 01	Stainless steel	0 880 16	0 880 27		
			Metal	Stainless steel	0 880 04	Stainless steel		0 880 46	
				Brass	0 880 07	Brass		0 880 49	
16 (2 x 8) modules		0 880 25	Plastic	0 880 02	Stainless steel	0 880 17	0 880 28		
			Metal	Stainless steel	0 880 05	Stainless steel		0 880 47	
				Brass	0 880 08	Brass		0 880 50	
Access covers 		For lid and trim with 8/12 modules	0 880 39	Plastic	0 880 00	Stainless steel	0 880 15	-	
				Metal	Stainless steel	0 880 03	Stainless steel		0 880 45
					Brass	0 880 06	Brass		0 880 48
	For lid and trim with 12/18 modules	0 880 40	Plastic	0 880 01	Stainless steel	0 880 16	-		
			Metal	Stainless steel	0 880 04	Stainless steel		0 880 46	
				Brass	0 880 07	Brass		0 880 49	
	For lid and trim with 16/24 modules	0 880 41	Plastic	0 880 02	Stainless steel	0 880 17	-		
			Metal	Stainless steel	0 880 05	Stainless steel		0 880 47	
				Brass	0 880 08	Brass		0 880 50	

MOUNTING PRINCIPLE

