

Mosaic™ Programme call units

for day hospitals, dialysis centres...



Selection chart for plates **p. 906**
Supports -Technical characteristics, **see e-catalogue**

Suitable for hotels, schools, non-medical residential homes
For centralisation of 1 to 6 calls via indicator lights
Call control via pushbutton
2 wires per direction
Registration of calls via numbered indicator lights and brief audible signal
Several calls can be registered simultaneously
Individual cancelling for each direction
Supplied with numbers
Possibility of using a 12 V protected supply for 12 V SELV units

Pack	Cat.Nos	Replacement cord
1	9 804 12 	With integrated power supply 127/230 V~ - 50/60 Hz
Call units to be equipped		
		6-direction modules Used to create call panels according to requirements 6 modules
1	0 766 55	With integrated power supply 127/230 V~ - 50/60 Hz
1	0 766 57	For external 12 V SELV power supply (not provided)

Pack	Cat.Nos	6-direction transfer unit
1	0 766 56	6 directions For remote transfer of calls 6 modules
10	0 783 62	Component for call unit NO/NC contact - 2 A Equipped with cord, length 2 m With 12 mm fixed-pitch for 2P socket Cat.No 0 771 50
10	0 771 50	Socket outlet 2P ELV screw terminals Automatic terminals - Antimicrobial ⁽¹⁾ 1 module

1: Contains a silver compound to prevent the growth of bacteria on the surface of the plate

Selection guide,
see e-catalogue

Wiring diagram,
see e-catalogue