

Legrand cabling system, LCS³ cat. 6A and cat. 7

cables and cords



Pack	Cat. No.	Cat. 6A cables for local networks
		Performance 500 MHz 4 pairs or 2x4 twisted pair cables, 100 Ω Yellow RAL 1018 LSZH sheath: zero halogen. ANSI/TIA colour code Compliant with ISO/IEC 11 801, EN 50173 and ANSI/TIA 568 standards Products conforming to the new CPR regulation (except Cat. No 0 327 87)
	LSZH	
500 ¹	0 327 87	U/UTP - 4 pairs Length 500 m. Supplied on reel. Weight 35 kg
500 ¹	0 327 78	F/UTP - 4 pairs Length 500 m. Supplied on reel. Weight 29.2 kg Euroclass Dca
500 ¹	0 328 78	F/UTP - 2 x 4 pairs Length 500 m. Supplied on reel. Weight 58 kg Euroclass Dca
500 ¹	0 328 83	F/FTP - 4 pairs Length 500 m. Supplied on reel. Weight 76 kg Euroclass Cca
500 ¹	0 327 99	Length 500 m. Supplied on reel. Weight 26 kg Euroclass Dca
500 ¹	0 327 98	F/FTP - 2 x 4 pairs Length 500 m. Supplied on reel. Weight 62 kg Euroclass Dca
500 ¹	0 328 84	U/FTP - 4 pairs Length 500 m. Supplied on reel. Weight 39 kg Euroclass Cca
500 ¹	0 328 85	U/FTP - 2 x 4 pairs Length 500 m. Supplied on reel. Weight 54 kg Euroclass Cca

Pack	Cat. No.	Cat. 7 cables for local networks
		Performance 600 MHz 4 twisted pair cables, 100 Ω LSZH sheath: zero halogen. ANSI/TIA colour code Compliant with ISO/IEC 11 801 and EN 50173 standards Products conforming to the new CPR regulation
	LSZH	
500 ¹	0 328 82	S/FTP - 4 pairs Length 500 m. Supplied on reel. Weight 45 kg Euroclass B2 ca
500 ¹	0 327 77	Length 500 m. Supplied on reel. Weight 33 kg Euroclass Dca
500 ¹	0 327 79	S/FTP - 2 x 4 pairs Length 500 m. Supplied on reel. Weight 58 kg Euroclass Dca

Pack	Cat. No.	Cat. 7 indoor/outdoor cable for local networks
		Performance 600 MHz 4 twisted pair cable, 100 Ω LSZH sheath: zero halogen. ANSI/TIA colour code Compliant with ISO/IEC 11 801 and EN 50173 standards Product conforming to the new CPR regulation
	LSZH	
500 ¹	0 338 90	S/FTP - 4 pairs - indoor/outdoor Length 500 m. Supplied on reel. Weight 45 kg Euroclass Eca

1: in metre(s)

Pack	Cat. No.	Cat. 6A RJ 45 patch cords and user cords
		RJ 45/RJ 45 - straight With special "easy grip" plug Compliant with ISO/IEC 11 801, EN 50173 and ANSI/TIA 568 standards
	PVC	
1	0 518 82	Unscreened U/UTP, impedance 100 Ω Length 1 m
1	0 518 83	Length 2 m
1	0 518 84	Length 3 m
1	0 518 85	Length 5 m
	LSZH	
1	0 518 78	Length 1 m
1	0 518 79	Length 2 m
1	0 518 80	Length 3 m
1	0 518 81	Length 5 m
1	0 518 74	Length 1 m
1	0 518 75	Length 2 m
1	0 518 76	Length 3 m
1	0 518 77	Length 5 m
	PVC	
		Shielded S/FTP, impedance 100 Ω
1	0 518 16	Length 0.5 m
5	0 517 80	Length 1 m
5	0 517 81	Length 2 m
5	0 517 82	Length 3 m
5	0 517 83	Length 5 m
	LSZH	
1	0 518 70	Length 1 m
1	0 518 71	Length 2 m
1	0 518 72	Length 3 m
1	0 518 73	Length 5 m
1	0 518 66	Length 1 m
1	0 518 67	Length 2 m
1	0 518 68	Length 3 m
1	0 518 69	Length 5 m

Pack	Cat. No.	Cat. 6A RJ 45 patch cords and user cords - High Density
		RJ 45/RJ 45 - straight With special "easy grip" plug Compliant with ISO/IEC 11 801, EN 50173 and ANSI/TIA 568 standards
	LSZH	
1	0 515 50	Shielded S/FTP, impedance 100 Ω Length 0.5 m
1	0 515 51	Length 1 m
1	0 515 52	Length 2 m
1	0 515 53	Length 3 m
1	0 515 54	Length 5 m