


ID	Description	Date	By	Appr.
A				

Model PPH1305W_{PART} [A]
Drawing PPH1305_PROCUS_{DRW}

>400 ≤ 1000	±0,8
>120 = 400	±0,5
>30 = 120	±0,3
>6 = 30	±0,2



NOTE! Unit of measurement: inch [mm]

Back panel materials	
Painted steel (white)	DC01 AmO + powder painting white RAL9003 (white) S=0.08 [2,0]
Galvanized steel	DX51D+Z275MAC, S=0.08 [2,0]
Aluminium	EN AW-5754 H22, S=0.10 [2,5]

>=6	±0,1
>0,5 <=3	±0,1

Part	Code	Description	Pcs	Weight [g]/pcs
Supplier: -	Tool No: -	Volume -	Weight [g]	

Material: _____ Ensto Mat: _____

Tolerance ISO 2768-m

ENSTO

Ensto Building Systems Finland

Scale	Date	20.02.23
1:3	By	AKu
A4	Checked	
Sheet No: 1 (1)	Ctrl	

Polybox back panel 14x12x6

Replaces:	
Replaced:	
Drw No:	A
Ref:	UBP...
Code:	PPH1305