


ID	Description	Date	By	Appr.
A				

Model PPH1306W_{-PART} [A]
Drawing PPH1306_PROCUS_{-DW}

>400 ≤ 1000	±0,8
>120 = 400	±0,5
>30 = 120	±0,3
>6 = 30	±0,2
> = 6	±0,1
>0,5 ≤ 3	±0,1





NOTE! Unit of measurement: inch [mm]

Back panel materials	
Painted steel (white)	DC01 AmO + powder painting white RAL9003 (white) S=0.08 [2,0]
Galvanized steel	DX51D+Z275MAC, S=0.08 [2,0]
Aluminium	EN AW-5754 H22, S=0.10 [2,5]

Part	Code	Description	Pcs	Weight [g]/pcs
Supplier: -		Tool No: -	Volume -	Weight [g]

Material: _____ Ensto Mat: _____

Tolerance ISO 2768-m	 		Polybox back panel 16x14x8	Replaces:	
	Ensto Building Systems Finland			Replaced:	
	Scale	Date		Drw No:	A
	1:3	20.02.23		Ref:	UBP...
	A4	By		Checked	Code:
Sheet No: 1 (1)	AKu	Ctrl	PPH1306		