







Model: NGRP506023-U\_NFL1.dwg  
 Drawing: NGRP506023-U\_NFL1.dwg  
 Tolerance ISO 2768-m  
 >0,5 =3 ±0,1  
 >6 =6 ±0,1  
 >30 =120 ±0,3  
 >120 =400 ±0,5  
 >400 =1000 ±0,8



Mounting feet  
NFL1 assembly  
1:2



C-C  
1:6  
Dimensions in mm [inches]

ID	Description	Date	By	Appr.
A				

Supplier:	Tool No:	Volume	Weight [g]	0
Material: Glass reinforced polyester		Ensto Mat:		
 <b>Ensto Finland Oy</b> Ensto Electrification		Replaces: Replaced: Drw No: <b>A</b> Ref: <b>Cubo N</b> Code: <b>NGRP506023.U</b>		
Scale	Date	<b>NGRP506023.U</b> <b>UI 508A Industrial panel enclosure</b>		
1:5	24.11.2016			
A3	By: KA			
Sheet No: 1 (1)	Checked:			
	Ctrl:			