



Model: NGRW806030P3SH_NFL1.dwg
 Drawing: NGRW806030P3SH_NFL1.dwg
 Tolerance ISO 2768-m
 >0,5 =3 ±0,1
 >6 =6 ±0,1
 >6 =30 ±0,2
 >30 =120 ±0,3
 >120 =400 ±0,5
 >400 =1000 ±0,8



ID	Description	Date	By	Appr.
A				



Supplier:		Tool No:		Volume	Weight [g]
Material: Glass reinforced polyester		Ensto Mat:			0
 Ensto Finland Oy Ensto Electrification				Replaces:	
Scale: 1:6		Date: 8.2.2017		Replaced:	
A3		By: KA		Drw No: A	
Sheet No: 1 (1)		Checked:		Ref: Cubo N	
		Ctrl:		Code: NGRW806030P3SH	

Dimensions in mm [inches]