



Ref. Certif. No.

HU-005995

IEC SYSTEM FOR MUTUAL RECOGNITION OF TEST CERTIFICATES FOR ELECTRICAL EQUIPMENT (IECEE) CB SCHEME

CB TEST CERTIFICATE

Product	Socket-outlets
Name and address of the applicant	LEGRAND Magyarország Villamossági Rendszerek Zrt. Ipartelepí út 14. 6600 Szentes Hungary
Name and address of the manufacturer	LEGRAND Magyarország Villamossági Rendszerek Zrt. Ipartelepí út 14. 6600 Szentes Hungary
Name and address of the factory <i>Note: When more than one factory, please report on page 2</i>	LEGRAND Magyarország Villamossági Rendszerek Zrt. Ipartelepí út 14. 6600 Szentes Hungary
Ratings and principal characteristics	250 V~, 16 A, IP20 / IP21 / IP44 For further details see CB Test Report.
Trademark / Brand (if any)	LEGRAND
Customer's Testing Facility (CTF) Stage used	N/A
Model / Type Ref.	SUS11, SUS12, 7 650 22 ("Seano" design) For detailed Type reference list see Additional information on Page 2 and 3. For accessories see CB Test Report.
Additional information (if necessary may also be reported on page 2)	See additional page(s) for further Additional information.
A sample of the product was tested and found to be in conformity with	IEC 60884-1:2022
As shown in the Test Report Ref. No. which forms part of this Certificate	HU25SEAN 001

This CB Test Certificate is issued by the National Certification Body



TÜV Rheinland InterCert Kft., MEEI Division
H-1143 Budapest, Gizella út 51-57., Hungary
Web: www.tuv.com

Date: 2025-10-20

Signature:

Tötös Tamás László

Additional information :

Type variants and reference numbers

Type reference	Designation and type of terminals	Reference number	Color	
SUS12	2P+E socket-outlet with shutters, screwless	7 651 20	white	
		7 652 20	aluminium	
		7 653 20	black	
		7 654 20	dark grey	
		7 651 22	red	
		7 652 22	green	
		7 653 22	yellow	
		7 654 22	orange	
		2P+E socket-outlet with shutters and lid, IP44, screwless	7 651 24	white
			7 652 24	aluminium
			7 653 24	black
			7 654 24	dark grey
2P+E socket-outlet with shutters and lid, IP21, screwless	7 651 23	white		
	7 652 23	aluminium		
	7 653 23	black		
	7 654 23	dark grey		

< List continues next page. >



Date: 2025-10-20

Signature:

as on page 1

Additional information :

Type reference	Designation and type of terminals	Reference number	Color
SUS12	2P+E socket-outlet with shutters and lid, IP44, with alike keyed lock, screwless	7 651 96	white
		7 652 96	aluminium *
		7 653 96	black *
		7 654 96	dark grey *
	2P+E socket-outlet with shutters and lid, IP44, with differently keyed lock, screwless	7 651 90	white
		7 652 90	aluminium *
		7 653 90	black *
		7 654 90	dark grey *
SUS11	2P+E socket-outlet without shutters, screwless	7 651 21	white
		7 652 21	aluminium
		7 653 21	black
		7 654 21	dark grey
7 650 22	2P+E socket-outlet with shutters (tamper proof) with screw	7 650 22	red

* with painted lids with their color.



Date: 2025-10-20

Signature:

as on page 1