



Ref. Certif. No.
SE-105240

IEC SYSTEM FOR MUTUAL RECOGNITION OF TEST CERTIFICATES FOR ELECTRICAL EQUIPMENT (IECEE) CB SCHEME

CB TEST CERTIFICATE

Product

Switched socket outlet, flush type

Name and address of the applicant

Legrand Intelligent Electrical (Huizhou) Co., Ltd.
Bldg. B1-B3, East No.39 Hechang 6th Rd.,
HZZK Hitech Industrial Development Zone, Huizhou,
Guangdong, China

Name and address of the manufacturer

LEGRAND FRANCE
128, Avenue du Maréchal de Lattre de Tassigny
87045 Limoges Cedex-France

Name and address of the factory

Note: When more than one factory, please report on page 2

Same as applicant

Ratings and principal characteristics

13A, 250V~, IP20, Class I

Trademark (if any)

legrand, tenby

Customer's Testing Facility (CTF) Stage used

-

Model / Type Ref.

See page 2

Additional information (if necessary may also be reported on page 2)

See page 2

A sample of the product was tested and found to be in conformity with

IEC 60884-1:2002+A1+A2
IEC 60884-2-3:2006
Standard sheet: Type G (Configuration of BS1363-2)

As shown in the Test Report Ref. No. which forms part of this Certificate

210502350SHA-001

This CB Test Certificate is issued by the National Certification Body

Intertek Semko AB
Torshamnsgatan 43
Box 1103
SE-164 22 Kista, Sweden

intertek

Signature:

Date: 21 June, 2021

Hyden Li

Model / Type Ref.

617146, 617346, 617446, 730076, 738028, 738029, 617646, 617746, 617846, 617647, 617747, 617847, 617649, 617749, 617849, 281113MW, 281113MB, 281113MG, 281113CH, 281113DB, 281113BA, 281113BB, 281113DS, 281115MW, 281115MB, 281115MG, 281115CH, 281115DB, 281115BA, 281115BB, 281115DS

Additional information

Flush type, rewirable, with two ways Type G outlets (configuration of BS 1363-2), with shutter, with single pole switch, with plastic cover plate or plastic lining combined with metal sheet cover plate, with or without metal frame, with design A or design B construction, with or without indicator lamp, see below for details:

617146: design A construction (style 1), with white enclosure
617346: design A construction (style 1), with dark grey enclosure
617446: design A construction (style 1), with brown enclosure
730076: design B construction, with white round enclosure
738028: design B construction, with white square enclosure
738029: design B construction, with white square enclosure, with indicator lamp.
617646: design A construction (style 2), with white enclosure
617746: design A construction (style 2), with anthracite enclosure
617846: design A construction (style 2), with ivory enclosure
617647: design A construction (style 2), with white enclosure, with indicator lamp
617747: design A construction (style 2), with anthracite enclosure, with indicator lamp
617847: design A construction (style 2), with ivory enclosure, with indicator lamp
617649: design A construction (style 2), with white insert and red plastic cover, with indicator lamp
617749: design A construction (style 2), with anthracite insert and red plastic cover, with indicator lamp
617849: design A construction (style 2), with ivory insert and red plastic cover, with indicator lamp.
281113MW, design A construction, with matt white enclosure, with metal frame
281113MB, design A construction, with matt black enclosure, with metal frame
281113MG, design A construction, with matt grey enclosure, with metal frame
281113CH, design A construction, with champagne enclosure, with metal frame
281113DB, design A construction, with dark bronze enclosure, with metal frame
281113BA, design A construction, with plastic lining combined with brushed aluminium metal sheet cover plate, with metal frame.
281113BB, design A construction, with plastic lining combined with brushed black metal sheet cover plate, with Metal frame.
281113DS, design A construction, with dark silver enclosure, with metal frame
281115MW, design A construction, with matt white enclosure, with metal frame, with indicator lamp on switch
281115MB, design A construction, with white enclosure, matt black enclosure, with metal frame, with indicator lamp on switch.
281115MG, design A construction, with matt grey enclosure, with metal frame, with indicator lamp on switch
281115CH, design A construction, with champagne enclosure, with metal frame, with indicator lamp on switch
281115DB, design A construction, with dark bronze enclosure, with metal frame, with indicator lamp on switch
281115BA, design A construction, with plastic lining combined with brushed aluminium metal sheet cover plate, with metal frame, with indicator lamp on switch.
281115BB, design A construction, with plastic lining combined with brushed black metal sheet cover plate, with metal frame, with indicator lamp on switch.
281115DS, design A construction, with dark silver enclosure, with metal frame, with indicator lamp on switch

style 1: plastic cover with arc shape, and front cover body without embossing pattern.

style 2: plastic cover with chamfering shape, and front cover body with some embossing pattern.

Date: 21 June, 2021

Signature:

