

IEC SYSTEM FOR MUTUAL RECOGNITION OF TEST CERTIFICATES FOR ELECTRICAL EQUIPMENT (IECEE) CB SCHEME

CB TEST CERTIFICATE

Product

Flexible conduits system

Name and address of the applicant

bticino S.p.A.
Viale Borri, 231, 21100 Varese (VA)
Italy

Name and address of the manufacturer

bticino S.p.A.
Viale Borri, 231, 21100 Varese (VA)
Italy

Name and address of the factory

LEGRAND FRANCE LORRAINE SA
89 Chemin de Montrichard Boite Postale 89, 54704 Pont à Mousson Cedex
France*Note: When more than one factory, please report on page 2* Additional information on page 2

Ratings and principal characteristics

Nominal diameter: 33 or 36 mm
Conduits classification coding: 1 3 3 3 4 0 6 6 – 1 1 1
Black or grey colour
(see also pages 5 and 6 of Test Report No. MI22-0082234-04).

Trademark / Brand (if any)

RTA 

RTA LEGRAND

Customer's Testing Facility (CTF) Stage used

CTF Stage 2

Model / Type Ref.

LGP-Standard series
(see also Additional Sheet)

Additional information (if necessary may also be reported on page 2)

 Additional information on page 2

A sample of the product was tested and found to be in conformity with

IEC 61386-1:2008, IEC 61386-1:2008/AMD1:2017, IEC 61386-23:2021

National differences:

EU Group Differences

As shown in the Test Report Ref. No. which forms part of this Certificate

MI22-0082234-04

This CB Test Certificate is issued by the National Certification Body

IMQ S.p.A.
Via Quintiliano 43
Milano, 20138
Italy

Date: 2024-01-31

Signature: Fabio Taormina

Description of the components of the flexible conduits system LGP-Standard series

Code	Description	Nominal diameter	Colour
666418	Flexible conduit	33 mm	Black
666406	Flexible conduit	36 mm	Grey
666485	Straight connector with M40 thread	33 mm	Black
666624	90° connector with M40 thread	33 mm	Black
666712	45° connector with M40 thread	33 mm	Black
666880	90° flanged connector	33 mm	Black
666969	Gasket	33 mm	—
666991	Fixing clip	33 mm	Black
666998	Top hat rails 35 mm wide fixing clip	29 mm to 33 mm	Black
666486	Straight connector with M40 thread	36 mm	Black
666487	Straight connector with M50 thread	36 mm	Black
666625	90° connector with M40 thread	36 mm	Black
666626	90° connector with M50 thread	36 mm	Black
666713	45° connector with M40 thread	36 mm	Black
666714	45° connector with M50 thread	36 mm	Black
666881	90° flanged connector	36 mm	Black
666970	Gasket IP68	36 mm	—