

Tanúsítvány Certificate



Tanúsítvány szám *Certificate No.* Oldal *Page*
UP 69267844 0001

Jegyzőkönyv szám *Test Report No.*
HU25NOKT 001

Kiadás dátuma *Date of Issue*
2025-07-02

Tanúsítvány Tulajdonos *Certificate Holder*
HELLINIKI LEGRAND SA
184A Kifissias Avenue
15231 Athens
Greece

Gyártóhely *Manufacturing Plant*
**Legrand Magyarország Villamossági
Rendszerek Zrt.**
Ipartelepi út 14
6600 Szentes
Hungary

Vizsgálati Jel *Test Mark*



Tanúsítás alapjául szolgáló előírások *Tested according to*
IEC 60884-1:2022

Tanúsított Termék *(Termék azonosítás)*
Certified Product (Product Identification)

"Valena Life", "Valena Allure" and "Valena In-matic" socket-outlets

Model / Type references

NDP12, NDS11, NDS12, NDS21, NDS22, 7 531 31, 7 531 32

Ratings

250 V~, 16 A, IP20, IP21 and IP44

Trademark

legrand

Remarks

For detailed type variant list and available accessories see annex of this certificate.

A tanúsítvány a fenti termék típusra vonatkozik. A tanúsítvány a TÜV Rheinland InterCert Kft. Vizsgálati, Ellenőrzési és Tanúsítási Szabályzatán alapszik. A tanúsított termék megfelel a fenti vizsgálati előírásoknak, a sorozatgyártása ellenőrzött. A MEEI megfeleléségi jel használatának joga engedélyezett a tanúsított terméken.

This certificate refers to the above mentioned product type. The certificate is based on the Testing, Inspection and Certification Regulation of TÜV Rheinland InterCert Kft. The certified product fulfils the above listed requirements and its manufacturing is subject to surveillance. The right to use the MEEI conformity mark is permitted on the certified product.

Tanúsító Szervezet
Certification Body

TÜV Rheinland InterCert Kft., MEEI Division – Product Certification
H-1143 Budapest, Gizella út 51-57., Hungary
www.tuv.com

Tamás László Tötös

Validity of certificate can be checked on www.CERTIPEDIA.com

Annex to certificate No. UP 69267844 0001

Page 1/4

Type variants

Type and description	Reference numbers		
	Valena In-matic	Valena Life	Valena Allure
2P socket outlet with screwless terminals and with shutters type NDP12	7 530 16 (without cover and frame)	7 531 16, 7 534 16* white, 7 532 16, 7 535 16* ivory, 7 533 16, 7 536 16* alu (with IP 20 cover and without frame)	—
2P+E socket outlet with screwless terminals and without shutters type NDS11	7 530 21 (without cover and frame)	7 531 21 white, 7 563 21 black, 7 532 21 ivory, 7 533 21 alu (with IP20 cover and without frame)	—
2P+E socket outlet with screwless terminals and with shutters type NDS12	7 530 20, 7 530 30* (without cover and frame)	7 531 20 (cover ED02410), 7 534 20*, 7 531 09** white, 7 563 09, 7 563 20 (cover ED02410) black, 7 532 20 (cover ED02410), 7 535 20*, 7 532 09** ivory, 7 533 20 (cover ED02410), 7 536 20*, 7 533 09** alu, 7 532 29 (cover ED02410) orange, 7 533 29 (cover ED02410) green, 7 531 29 red (with IP20 cover and without frame)	7 548 85, 7 537 20*, 7 558 93** white, 7 548 86, 7 538 20*, 7 558 94** ivory, 7 548 87, 7 539 20*, 7 558 95** alu, 7 548 88, 7 539 30*, 7 558 96** black, 7 548 89 pearl, (with IP20 cover and without frame);
		7 557 40 white, 7 557 41 ivory (with IP20 cover and frame)	—
		7 531 17 white, 7 532 17 ivory, 7 533 17 alu (with IP21 cover and without frame);	7 551 55 white (with IP21 cover and without frame);
		7 531 19 (with IP44 cover EC00230, white base ED03555 and waterproofness ring GD00335, without frame)	7 552 04 (with IP44 cover and without frame)

< List continues next page >

Certification Body
Date of issue:

Budapest, 2025-07-02



.....

Tamás László Tötös

Annex to certificate No. UP 69267844 0001

Page 2/4

Type and description	Reference numbers		
	Valena In-matic	Valena Life	Valena Allure
2P+E socket outlet with screw-type terminals and without shutters type NDS21	7 530 25 (without cover and frame)	7 531 25, 7 534 25* white, 7 532 25, 7 535 25* ivory, 7 533 25, 7 536 25* alu (with IP 20 cover and without frame)	7 537 25* white, 7 538 25* ivory, 7 539 35* alu 7 539 45* black
2P+E socket outlet with screw-type terminals and with shutters type NDS22	7 530 24, 7 530 29* (without cover and frame)	7 531 24, 7 534 24* white, 7 532 24, 7 535 24* ivory, 7 533 24, 7 536 24* alu (with IP 20 cover and without frame)	7 537 24* white, 7 538 24*, 7 558 98** ivory, 7 539 24*, 7 558 99** alu, 7 539 34*, 7 559 00** black (with IP 20 cover and without frame)
2P+E socket outlet with screw-type terminals and with shutters (tamper proof)	—	7 531 31 red (with IP20 cover 933, with white ring CH00221, without frame)	7 531 32 red (with IP20 cover ED02673 and without frame)
* Country-specific reference numbers. ** Reference numbers of socket-outlet which deliver other market (Distribution of energy (DIY)) Remark: Reference numbers in the same cell are technically identical.			

< For accessories see next pages >

TÜVRheinland

Certification Body
Date of issue:

Budapest, 2025-07-02



 Tamás László Tötös

Annex to certificate No. UP 69267844 0001

Page 3/4

Accessories for design "Valena Allure"

	Reference numbers				
	white	ivory	alu	black	pearl
Cover 2P	7 549 75	7 549 76	7 549 77	7 549 78	7 549 79
Cover 2P+E	7 552 05	7 552 06	7 552 07	7 552 08	7 552 09
Cover 2P+E with lid	7 548 45	7 548 46	7 548 47	7 548 48	7 548 49
Cover 2P+E with indicator window	7 548 55	7 548 56	7 548 57	7 548 58	7 548 59
Surface mounting box (1 gang)	7 555 51	7 555 61	7 555 71	—	—
Surface mounting box (2 gangs)	7 555 52	7 555 62	7 555 72	—	—
Blank plate (1 gang)	7 551 85	7 551 86	7 551 87	—	—

Frames (plates)

Design	Color	1 gang	2 gang	3 gang	4 gang	5 gang	5 modules
basic	white	7 543 01	7 543 02	7 543 03	7 543 04	7 543 05	7 543 06
	ivory	7 543 11	7 543 12	7 543 13	7 543 14	7 543 15	7 543 16
paint	aluminium	7 543 91	7 543 92	7 543 93	7 543 94	7 543 95	7 543 96
	matt black	7 544 01	7 544 02	7 544 03	7 544 04	7 544 05	7 544 06
	pearl	7 544 11	7 544 12	7 544 13	7 544 14	7 544 15	7 544 16
graph	narcis chrome	7 543 41	7 543 42	7 543 43	7 543 44	7 543 45	—
	narcis gold	7 543 51	7 543 52	7 543 53	7 543 54	7 543 55	—
plating material	white mirror	7 544 21	7 544 22	7 544 23	7 544 24	7 544 25	—
	black baroque	7 544 31	7 544 32	7 544 33	7 544 34	7 544 35	—
	purple baroque	7 544 41	7 544 42	7 544 43	7 544 44	7 544 45	—
	leather	7 544 51	7 544 52	7 544 53	7 544 54	7 544 55	—
	walnut	7 544 61	7 544 62	7 544 63	7 544 64	7 544 65	—
	carbon	7 544 71	7 544 72	7 544 73	7 544 74	7 544 75	—
	stainless steel	7 542 81	7 542 82	7 542 83	7 542 84	7 542 85	—
	dark stainless steel	7 542 91	7 542 92	7 542 93	7 542 94	7 542 95	—
	wires	7 544 91	7 544 92	7 544 93	7 544 94	7 544 95	—
	place marble	7 555 21	7 555 22	7 555 23	—	—	—
	black glass	7 555 31	7 555 32	7 555 33	7 555 34	7 555 35	—
	white glass	7 555 41	7 555 42	7 555 43	7 555 44	7 555 45	—

< For further accessories see next page >

Certification Body
Date of issue:

Budapest, 2025-07-02



.....

Tamás László Tötös

Annex to certificate No. UP 69267844 0001

Page 4/4

Accessories for design "Valena Life"

	Reference numbers			
	white	ivory	alu	black / matt black
Cover 2P	7 549 70	7 549 71	7 549 72	7 569 72
Cover 2P+E	7 552 00	7 552 01	7 552 02	7 562 02
Cover 2P+E with lid	7 548 40	7 548 41	7 548 42	7 568 42
Cover 2P+E with indicator lamp	7 548 50	7 548 51	7 548 52	—
Surface mounting box (1 gang)	7 541 91	7 542 01	7 542 11	7 540 66
Surface mounting box (2 gang)	7 541 92	7 542 02	7 542 12	7 540 67
Cable outlet cover	—	—	—	7 567 32
Blanking plate (1 poste)	7 551 80	7 551 81	7 551 82	7 540 68
Support frame + plate (4x2 modules)	7 521 45	—	7 523 45	—
Support frame + plate (2x4x2 modules)	7 521 46	—	7 523 46	—
Adaptor for base of "Mosaic" socket-outlet	7 521 44	—	7 523 44	—

Frames (plates)

Design	Color	1 gang	2 gang	3 gang	4 gang	5 gang	5 modules
basic	white	7 540 01 7 540 07*	7 540 02	7 540 03	7 540 04	7 540 05	7 540 06
	ivory	7 540 41 7 540 47*	7 540 42	7 540 43	7 540 44	7 540 45	7 540 46
color	terracotta	7 540 71	7 540 72	7 540 73	7 540 74	7 540 75	—
	lime	7 540 81	7 540 82	7 540 83	7 540 84	7 540 85	—
	adria	7 540 91	7 540 92	7 540 93	7 540 94	7 540 95	—
paint full	aluminium	7 541 31 7 541 37*	7 541 32	7 541 33	7 541 34	7 541 35	7 541 36
	pearl	7 541 41	7 541 42	7 541 43	7 541 44	7 541 45	—
	mat black	7 542 51	7 542 52	7 542 53	7 542 54	7 542 55	—
	graphite	7 542 71	7 542 72	7 542 73	7 542 74	7 542 75	—
basic+	white / chrome	7 540 31	7 540 32	7 540 33	7 540 34	7 540 35	—
	ivory / gold	7 540 61	7 540 62	7 540 63	7 540 64	7 540 65	—
fake imitation	dark wood	7 541 71	7 541 72	7 541 73	7 541 74	7 541 75	—
	light wood	7 541 81	7 541 82	7 541 83	7 541 84	7 541 85	—
	inox style	7 541 51	7 541 52	7 541 53	7 541 54	7 541 55	—
	copper style	7 541 61	7 541 62	7 541 63	7 541 64	7 541 65	—
labelholder	white	7 540 11	7 540 12	7 540 13	—	—	—
	ivory	7 540 51	7 540 52	7 540 53	—	—	—
IP44	white	7 540 21	—	—	—	—	—

* Country-specific reference numbers.

Remark: Reference numbers in the same cell are technically identical.

Certification Body
Date of issue:

Budapest, 2025-07-02



.....

Tamás László Tötös