

**LCIE N° : NF012\_4577**

Titulaire :  
*License Holder:*

**LEGRAND FRANCE**  
128 AVENUE DU MARECHAL DE LATTRE DE TASSIGNY  
87045 LIMOGES CEDEX  
France

Site de fabrication :  
*Factory:*

1456AP

Produit :  
*Product:*

**Interrupteur pour installations électriques fixes  
domestiques et analogues**  
*Switch for household and similar fixed electrical installations*

Marque commerciale (s'il y a lieu) :  
*Trade mark (if any):*



Modèle, type, référence :  
*Model, type, reference:*

Series / Gamme : **CELIANE**  
Voir Annexe / *See Annex*

Caractéristiques principales :  
*Main characteristics:*

Voir Annexe / *See Annex*

Informations complémentaires :  
*Additional information:*

/

Le produit est conforme à :  
*The product is in conformity with:*

EN 60669-1:2018

Documents pris en compte :  
*Relevant documents:*

TR n° 23848234-805359 Version 01  
TR N° HU24CENA 001 / Certificat OC N° HU-005107

Annule et remplace (s'il y a lieu) :  
*Cancel and replaces (if necessary):*

/

En vertu de la présente décision notifiée par le LCIE organisme mandaté, AFNOR Certification accorde le droit d'usage de la Marque NF à la société qui en est titulaire pour les produits visés ci-dessus, dans les conditions définies par les règles générales de la Marque NF et par les règles de certification NF, pour autant que les contrôles réguliers de la fabrication et les vérifications par tierce partie soient satisfaisants.

*On the strength of the present decision notified by LCIE mandated certification body, AFNOR Certification grants the right to use the NF Mark to the licence holder for the above mentioned products, within the frame of the general rules of the NF Mark and of the NF certification rules, as far as the regular checking and third party verifications of the production are satisfactory.*

Fontenay-aux-Roses, 17/12/2024

Date de fin de validité / *Expiry date* :

La validité de la présente licence cesse dès l'annulation de l'une des normes sur lesquelles elle est fondée.  
*The present license is valid until the cancellation of one of the standards on which it is based.*



**LABORATOIRE CENTRAL DES  
INDUSTRIES ELECTRIQUES**  
S.A.S au capital de 15.745.984 €  
RCS Nanterre B 408 363 174  
33 avenue du Général Leclerc  
F - 92266 FONTENAY AUX ROSES

**Julien GAUTHIER**  
Responsable Certification/Certification Officer

**RÉFÉRENCES - CARACTÉRISTIQUES PRINCIPALES**  
**REFERENCES - MAIN CHARACTERISTICS**

Mechanisms

Type Reference	References	PRO/DIY	Pattern	Characteristics	Type of Terminals	Method of actuating	Pilot light	Specificity	Making Up
Without	CM0006	PRO	6	10AX 250V~	Screwless type	Rocker	Without	Sans enjoliveur et plaque Without cover and cover plate	
	CM1006						Locator		CM0006 + CM0227
	CM2006						Indicator		CM0006 + CM0228
Without	CM0030	PRO	6	6A 250V~	Screwless type	Momentary Rocker	Without	Sans enjoliveur et plaque Without cover and cover plate	
	CM1030						Locator		CM0030 + CM0227

"All the commercial references listed above may be supplemented with a prefix of type LG-, BT-, ... (to indicate the brand) and/or suffix of type 0, 1, 2, 3, 4, FI, EX, ...

In this case, the products are technically the same."

"Toutes les références commerciales énumérées ci-dessus peuvent être complétées par un préfixe du type LG-, BT-, ... (pour indiquer la marque) et/ou un suffixe du type 0, 1, 2, 3, 4, FI, EX, ...

Dans ce cas, les produits sont techniquement les mêmes".

**Classification**

Function / Patern number	6
Contact opening ( gap )	Normal-gap
Degree of protection (IP)	IP20
Level of shock resistance (IK)	IK02
Method of actuating	See Table
Method of mounting	Flush type / Surface type with box for surface mounting
Method of installation	Design A
Type of terminals	Screwless type ( rigid and flexible )
Rated current (A)	6A, 10AX - See Table
Rated voltage (V)	250V~

Accessories

Voyants / Pilot light

References	Designation	Specificity
CM0227	Voyant lumineux enjoliveur anneau Locator LED ring rocker	230V~ 0,17mA
CM0228	Voyant témoin enjoliveur anneau Indicator LED ring rocker	230V~ 2,4mA

### Enjoliveur / Cover

Reference	Designation
CB0006	Enjoliveur anneau verre Onyx Noir Black Onyx glass ring cover
CB1006	Enjoliveur anneau verre Blanc White glass ring cover
CB2006	Enjoliveur anneau verre nickel Nickel glass ring cover
CB3006	Enjoliveur anneau verre nickel sombre Dark nickel glass ring cover
CB4006	Enjoliveur anneau chêne Oak ring cover
CB5006	Enjoliveur anneau frêne wengué Ash wengue ring cover
CB6006	Enjoliveur anneau porcelaine Porcelain ring cover

### Plaques / Cover Plate - Entraxe 71mm - DECO

Nbr de postes / modules Number of gang / module	BLANC EMAILLE ENAMELLED WHITE		IVOIRE IVORY		BLEU DE FOUR BLEU DE FOUR		JAUNE SAFFRAN SAFFRON YELLOW	VERT CELADON CELADON GREEN		
	PRO	DIY	PRO	DIY	PRO	DIY	PRO	DIY	PRO	DIY
1 poste / 1 gang	CP0001	CP0021	CP0201	-	CP0301	CP0321	CP0401	CP0421	CP0501	CP0521
2 postes / 2 gang	CP0002	CP0022	CP0202	-	CP0302	CP0322	CP0402	CP0422	CP0502	CP0522
3 postes / 3 gang	CP0003	CP0023	CP0203	-	CP0303	CP0323	CP0403	CP0423	CP0503	CP0523
4 postes / 4 gang	CP0004	CP0024	CP0204	-	CP0304	CP0324	CP0404	CP0424	CP0504	CP0524

### Plaques / Cover Plate - Entraxe 71mm - DECO MAT

Nbr de postes / modules Number of gang / module	NOIR MAT MAT BLACK		BLEU ORAGE STORM BLUE		GRIS CENDRE ASH GREY		BLANC AMANDE ALMOND WHITE	
	PRO	DIY	PRO	DIY	PRO	DIY	PRO	DIY
1 poste / 1 gang	CP0101	CP0121	CP0901	CP0921	CP1001	CP1021	CP1101	CP1121
2 postes / 2 gang	CP0102	CP0122	CP0902	CP0922	CP1002	CP1022	CP1102	CP1122
3 postes / 3 gang	CP0103	CP0123	CP0903	CP0923	CP1003	CP1023	CP1103	CP1123
4 postes / 4 gang	CP0104	CP0124	CP0904	CP0924	CP1004	CP1024	CP1104	CP1124

### Plaques / Cover Plate - Entraxe 71mm - GRAPHIQUE

Nbr de postes / modules Number of gang / module	BLANC RELIEF RELIEFED WHITE		NOIR METEORE METEOR BLACK	
	PRO	DIY	PRO	DIY
1 poste / 1 gang	CP0601	CP0621	CP0701	CP0721
2 postes / 2 gang	CP0602	CP0622	CP0702	CP0722
3 postes / 3 gang	CP0603	CP0623	CP0703	CP0723
4 postes / 4 gang	CP0604	CP0624	CP0704	CP0724

### Plaques / Cover Plate - Entraxe 71mm - ANODIZEE

Nbr de postes / modules Number of gang / module	LAITON SATINE SATIN BRASS		BRONZE SATINE SATIN BRONZE		ALUMINIUM SATINE SATIN ALUMINIUM		ACIER SATINE SATIN STEEL	
	PRO	DIY	PRO	DIY	PRO	DIY	PRO	DIY
1 poste / 1 gang	CP1201	CP1221	CP1601	CP1621	CP1701	CP1721	CP1801	CP1821
2 postes / 2 gang	CP1202	CP1222	CP1602	CP1622	CP1702	CP1722	CP1802	CP1822
3 postes / 3 gang	CP1203	CP1223	CP1603	CP1623	CP1703	CP1723	CP1803	CP1823
4 postes / 4 gang	CP1204	CP1224	CP1604	CP1624	CP1704	CP1724	CP1804	CP1824

### Plaques / Cover Plate - Entraxe 71mm - RETROS

Nbr de postes / modules Number of gang / module	LIEGE CORK		HETRE BEECH		FEUTRE FELT	
	PRO	DIY	PRO	DIY	PRO	DIY
1 poste / 1 gang	CP1301	CP1321	CP1401	CP1421	CP1501	CP1521
2 postes / 2 gang	CP1302	CP1322	CP1402	CP1422	CP1502	CP1522
3 postes / 3 gang	CP1303	CP1323	CP1403	CP1423	CP1503	CP1523
4 postes / 4 gang	CP1304	CP1324	CP1404	CP1424	CP1504	CP1524

### Plaques / Cover Plate - Entraxe 71mm - VERRE - METAL

Nbr de postes / modules Number of gang / module	VERRE ONYX NOIR ONYX BLACK GLASS	VERRE OPALE BLANC OPAL WHITE GLASS	NICKEL SATINE SATIN NICKEL	NICKEL SOMBRE SATINE SATIN DARK NICKEL
	PRO	PRO	PRO	PRO
1 poste / 1 gang	CP1901	CP2001	CP2101	CP2201
2 postes / 2 gang	CP1902	CP2002	CP2102	CP2202
3 postes / 3 gang	CP1903	CP2003	CP2103	CP2203
4 postes / 4 gang	CP1904	CP2004	CP2104	CP2204

Plaques / Cover Plate - Entraxe 71mm - BOIS - PORCELAINE

Nbr de postes / modules Number of gang /module	CHENE OAK	FRENE WENGE ASH WENGE	PORCELAINE PORCELAIN
	PRO	PRO	PRO
1 poste / 1 gang	CP2401	CP2501	CP2301
2 postes / 2 gang	CP2402	CP2502	CP2302
3 postes / 3 gang	CP2403	CP2503	CP2303
4 postes / 4 gang	CP2404	CP2504	

Cadre Saillie / Box for surface mounting

1 poste 2 modules	2 postes 4 modules	3 postes 6 modules	Couleur / Color	PRO / DIY
CB0231	CB0232	CB0233	Blanc / White	PRO
CN0231	CN0232	CN0233	Noir /Black	PRO
CX0231	CX0232		Blanc / White	DIY
CZ0231			Noir /Black	DIY