

IEC SYSTEM FOR MUTUAL RECOGNITION OF TEST CERTIFICATES FOR ELECTRICAL EQUIPMENT (IECEE) CB SCHEME**CB TEST CERTIFICATE**

Product

Fixed socket-outlet (Flush type)

Name and address of the applicant

Legrand Intelligent Electrical (Huizhou) Co., Ltd.
Bldg. B1-B3, East No.39 Hechang 6th Rd., HZZK Hi-tech
Industrial Development Zone, Huizhou, Guangdong, China

Name and address of the manufacturer

LEGRAND FRANCE
128, Avenue du Maréchal de Lattre de Tassigny 87045 LIMOGES
Cedex-FRANCE

Name and address of the factory

Note: When more than one factory, please report on page 2

See page 2

Ratings and principal characteristics

13A 250V~ 50/60Hz, IP20, Class I

Trademark (if any)

legrand

Customer's Testing Facility (CTF) Stage used

-

Model / Type Ref.

617*57, 28**33, K8/426/13/U***-HK, 57****, 282440***, 678146,
281133**

Additional information (if necessary may also be reported on page 2)

See page 2-3

A sample of the product was tested and found to be in conformity with

IEC 60884-1:2002+A1+A2

As shown in the Test Report Ref. No. which forms part of this Certificate

201201698SHA-001

This CB Test Certificate is issued by the National Certification Body

Intertek Semko AB
Torshamnsgatan 43
Box 1103
SE-164 22 Kista, Sweden**intertek**

Signature:

Hyden Li



Date: 10 May, 2021

Factories

Legrand (Beijing) Electrical Co., Ltd
No.4, Chaoqian Road, Changping Kejiyuanqu, Beijing, China

Legrand Intelligent Electrical (Huizhou) Co., Ltd.
Bldg. B1-B3, East No.39 Hechang 6th Rd.,HZZK Hi-tech Industrial Development Zone, Huizhou, Guangdong, China

LEGRAND Magyarország Villamossági Rendszerek Zrt.
Ipartelepi út 14, H-6600, SZENTES, Csongrád HUNGARY

Additional information

13A 250V~ 50/60Hz, flush type, IP20, Class I, rewirable, with one way Type G outlets (configuration of BS 1363-2), with shutters, with USB charger which evaluated according to IEC 62368-1:2018 which in conjunction with IEC 62368-3:2017 with report no. 200302050SHA-001, with metal cover, or with plastic cover plate or plastic lining combined with metal sheet cover plate, or without cover plate, with or without metal frame, all type with same construction, only with different cover plate.

617*57	617057	with plastic cover with arc transition chamfer, with front cover without embossing pattern	white colour
	617257		ivory colour
	617357		dark grey colour
	617457		brown colour
	617657	with plastic cover with angle chamfer, with front cover with embossing pattern	white colour
	617757		anthracite colour
	617857		ivory colour

28**33	281133	plastic cover	White colour
	283133		silver colour
	283333		pearl colour
	283533		dark silver colour
	283933		champagne colour

K8/426/13/U***-HK	K8/426/13/U-HK	plastic cover	White colour
	K8/426/13/U-C-HK		Matt black colour
	K8/426/13/U-C1-HK		rose gold colour
	K8/426/13/U-C2-HK		champagne colour
	K8/426/13/U-C3-HK		dark silver colour
	K8/426/13/U-C4-HK		Pink colour

57****	572158	without cover	White colour
	572658		Magnesium colour
	570082		Soft ALU colour
	571082		Champagne colour

Date: 10 May, 2021

Signature:



Additional information

282440***	282440	plastic cover	White colour
	282440-C		Matt black colour
	282440-C1		rose gold colour
	282440-C2		champagne colour
	282440-C3		dark silver colour
281133**	281133MW	plastic cover	Matt White
	281133MG		Matt Grey
	281133MB		Matt Black
	281133DS		Dark Sliver
	281133CH		Champagne
	281133DB		Dark Bronze
	281133BA	plastic lining combined with metal sheet cover plate, metal frame	BRUSHED ALUMINIUM
	281133BB		BRUSHED BLACK

678146: design A construction, without cover, white colour, all test evaluated when with mated plastic cover or metal cover which provided by the manufacturer as far as possible.

For 282440*** series and K8/426/13/U***-HK series, they with total same construction, only different type designation according to client's request.

For 57*** series, all test evaluated when with mated plastic cover or metal cover which provided by the manufacturer as far as possible.

Date: 10 May, 2021

Signature:

