OVE Austrian Electrotechnical Association

Eschenbachgasse 9 | 1010 Wien | Austria

ZVR: 327279890 | www.ove.at

OVE Certification

Kahlenberger Str. 2A | 1190 Wien | Austria T +43 1 370 58 06 | certification@ove.at

Validity of ÖVE-Certificates can be checked at www.ove.at



Page 1 of 7

ÖVE-CERTIFICATE

including the entitlement to use the Austrian Safety Mark



Certificate No.: 131-288-00 Valid from: 2023 08 18

until: 2024 08 18

The Austrian Electrotechnical Association (OVE) hereby grants the right to the company mentioned below to label the listed products with the Austrian Safety Mark.

Certificate holder: **Legrand Austria GmbH**

Floridsdorfer Hauptstraße 1

1210 Wien Austria

Switches for household and similar fixed installations Product:

The products submitted by the applicant were type tested in accordance with the requirements of the technical standards and specifications listed in this certificate. OVE certifies the conformity of the listed products and those products manufactured strictly identical to the submitted ones (EN ISO/IEC 17067, Conformity Assessment Scheme Type 5).

The manufacturing process and the products are subject to ongoing surveillance based on harmonized European procedures. This certificate has been issued under the presumption and conditional on the fact that the certificate holder holds all necessary legal rights with regard to the product, presented for the testing and certification.

Results of testing are shown in file No(s):: 3749-1871/23

Österreichischer Verband für Elektrotechnik

Head of OVE Certification

Digitally signed by T. Neumayer

ipl.-Ing. T. Neumayer

Wien, 2023 08 18







Date: 2023 08 18 Page 2 of 7

Manufacturer:

Legrand Austria GmbH Floridsdorfer Hauptstraße 1 1210 Wien Austria

Factory location(s):

Legrand Magyarorszag Villamossagi Rendszerek Zrt. Ipartelepi ut. 14 pf. 10 6600 Szentes Hungary

Tested and certified according to:

OVE EN 60669-1:2019-04-01

This certificate is the basis for the EU Declaration of Conformity and the CE Marking by the manufacturer or his agent and shows the conformity of the certified product(s) with the listed standards as defined by the EU Low-Voltage Directive 2014/35/EU. For the presumption of conformity according to Art. 12 with the safety objectives according to Art. 3 of the Directive, transitional periods given in the Official Journal of the European Union have to be observed.

Product: Switches for household and similar fixed installations

Type designation: Trademark: Rating:

Series SEANO
Rated voltage: AC 250 V
Rated current: 6 A, 10 A, 10 AX
IP20 or IP44 (with sealing kit)

screw or screwless terminals

see type list

LEGRAND







Date: 2023 08 18

Page 3 of 7

Ref. Nr.	Type reference	Designation	Type of terminals	Color
7 650 06	SU004	Two-way switch (mechanism only), 10AX	screwless	white
7 650 10	SU004N	Two-way switch with plus neutral terminal (mechanism only), 10AX	screwless	white
7 650 08	SU005	Two-way two gang switch (mechanism only), 10AX	screwless	white
7 650 05	SU003	One-way two gang switch (mechanism only), 10AX	screwless	white
7 650 02	BI10V1	Two-pole switch (mechanism only), 10AX	screw	white
7 650 07	PE10V2	Intermediate switch (mechanism only), 10AX	screw	white
7 650 11	SU007P	Two-way push-button (mechanism only), 10A	screwless	white
7 650 17	SU008P	Two-way push button with plus neutral terminal (mechanism only), 10A	screwless	white
7 651 18	CO26P	Pull-cord changeover push-button, 6A	screwless	white
7 650 18	SU005P	Two-way two gang push-button (mechanism only), 10A	screwless	white







Date: 2023 08 18

Page 4 of 7

Accessories:

Ref nr.	Designation	Color
7 650 44	IP44 kit for single functions	transparent
7 650 45	IP44 kit for double functions	transparent
7 651 44	1 GANG frame IP44	white
7 652 44	1 GANG frame IP44	aluminium
7 653 44	1 GANG frame IP44	black
7 654 44	1 GANG frame IP44	dark grey
7 651 98	Surface mounting box 1 GANG	white
7 652 98	Surface mounting box 1 GANG	aluminium
7 653 98	Surface mounting box 1 GANG	black
7 654 98	Surface mounting box 1 GANG	dark grey
7 651 99	Surface mounting box 2 GANG	white
7 652 99	Surface mounting box 2 GANG	aluminium
7 653 99	Surface mounting box 2 GANG	black
7 654 99	Surface mounting box 2 GANG	dark grey
7 651 71	1G frame	white
7 651 72	2G frame	white
7 651 73	3G frame	white
7 651 74	4G frame	white
7 651 75	5G frame	white
7 656 71	1G frame with labelholder	white
7 656 72	2G frame with labelholder, horizontal	white
7 656 73	3G frame with labelholder, horizontal	white
7 656 74	4G frame with labelholder, horizontal	white
7 657 72	2G frame with labelholder, vertical	white
7 657 72	3G frame with labelholder, vertical	white
7 657 72	4G frame with labelholder, vertical	white
7 652 71	1G frame	aluminium





Date: 2023 08 18

Page 5 of 7

Ref nr.	Designation	Color	
7 652 72	2G frame	aluminium	
7 652 73	3G frame	aluminium	
7 652 74	4G frame	aluminium	
7 652 75	5G frame	aluminium	
7 653 71	1G frame	black	
7 653 72	2G frame	black	
7 653 73	3G frame	black	
7 653 74	4G frame	black	
7 653 75	5G frame	black	
7 654 71	1G frame	dark grey	
7 654 72	2G frame	dark grey	
7 654 73	3G frame	dark grey	
7 654 74	4G frame	dark grey	
7 654 75	5G frame	dark grey	
7 655 71	1G frame	pearl	
7 655 72	2G frame	pearl	
7 655 73	3G frame	pearl	
7 655 74	4G frame	pearl	
7 655 75	5G frame	pearl	
7 651 81	1G frame	premium white	
7 651 82	2G frame	premium white	
7 651 83	3G frame	premium white	
7 651 84	4G frame	premium white	
7 651 85	5G frame	premium white	
7 652 81	1G frame	premium aluminium	
7 652 82	2G frame	premium aluminium	
7 652 83	3G frame	premium aluminium	
7 652 84	4G frame	premium aluminium	
7 652 85	5G frame	premium aluminium	





Date: 2023 08 18

Page 6 of 7

Ref nr.	Designation	Color	
7 653 81	1G frame	premium black	
7 653 82	2G frame	premium black	
7 653 83	3G frame	premium black	
7 653 84	4G frame	premium black	
7 653 85	5G frame	premium black	
7 654 81	1G frame	premium dark grey	
7 654 82	2G frame	premium dark grey	
7 654 83	3G frame	premium dark grey	
7 654 84	4G frame	premium dark grey	
7 654 85	5G frame	premium dark grey	
7 655 81	1G frame	premium mastic	
7 655 82	2G frame	premium mastic	
7 655 83	3G frame	premium mastic	
7 655 84	4G frame	premium mastic	
7 655 85	5G frame	premium mastic	
7 656 81	1G frame	premium titanium	
7 656 82	2G frame	premium titanium	
7 656 83	3G frame	premium titanium	
7 656 84	4G frame	premium titanium	
7 656 85	5G frame	premium titanium	
7 661 01	1G frame	premium white glass	
7 661 02	2G frame	premium white glass	
7 661 03	3G frame	premium white glass	
7 661 04	4G frame	premium white glass	
7 661 11	1G frame	premium smoked glass	
7 661 12	2G frame	premium smoked glass	
7 661 13	3G frame	premium smoked glass	
7 661 14	4G frame	premium smoked glass	
7 651 91	1G frame	premium carbon	





Date: 2023 08 18

Page 7 of 7

Ref nr.	Designation	Color	
7 651 92	2G frame	premium carbon	
7 651 93	3G frame	premium carbon	
7 651 94	4G frame	premium carbon	
7 653 91	1G frame	premium stainless steel	
7 653 92	2G frame	premium stainless steel	
7 653 93	3G frame	premium stainless steel	
7 653 94	4G frame	premium stainless steel	
7 654 91	1G frame	premium dark stainless steel	
7 654 92	2G frame	premium dark stainless steel	
7 654 93	3G frame	premium dark stainless steel	
7 654 94	4G frame	premium dark stainless steel	
7 652 91	1G frame	premium light wood matt black	
7 652 92	2G frame	premium light wood matt black	
7 652 93	3G frame	premium light wood matt black	
7 652 94	4G frame	premium light wood matt black	
7 661 21	1G frame	premium slade	
7 661 22	2G frame	premium slade	
7 661 23	3G frame	premium slade	
7 661 24	4G frame	premium slade	
7 661 31	1G frame	premium dark wood	
7 661 32	2G frame	premium dark wood	
7 661 33	3G frame	premium dark wood	
7 661 34	4G frame	premium dark wood	
7 661 41	1G frame	premium medium wood	
7 661 42	2G frame	premium medium wood	
7 661 43	3G frame	premium medium wood	
7 661 44	4G frame	premium medium wood	

