


## IEC SYSTEM FOR MUTUAL RECOGNITION OF TEST CERTIFICATES FOR ELECTRICAL EQUIPMENT (IECEE) CB SCHEME

## CB TEST CERTIFICATE

Product	Switched socket-outlet (flush-type)
Name and address of the applicant	Legrand Intelligent Electrical (Huizhou) Co., Ltd. Bldg. B1-B3, East No.39 Hechang 6th Rd., HZZK Hi-tech Industrial Development Zone, Huizhou, Guangdong CHINA
Name and address of the manufacturer	LEGRAND FRANCE 128, Avenue du Maréchal de Lattre de Tassigny 87045 Limoges Cedex FRANCE
Name and address of the factory <i>Note: When more than one factory, please report on page 2</i>	Same as applicant
Ratings and principal characteristics	13A, 250V~, IP20
Trademark (if any)	legrand
Customer's Testing Facility (CTF) Stage used	-
Model / Type Ref.	See page 2
Additional information (if necessary may also be reported on page 2)	See page 2
A sample of the product was tested and found to be in conformity with	IEC 60884-1:2002+A1+A2 IEC 60884-2-3:2006
As shown in the Test Report Ref. No. which forms part of this Certificate	210100292SHA-001

This CB Test Certificate is issued by the National Certification Body

Intertek Semko AB  
Torshamnsgatan 43  
Box 1103  
SE-164 22 Kista, Sweden

Signature: 

Hyden Li

Date: 09 March, 2021



Ref. Certif. No.

**SE-104113**

**Model / Type Ref.**

6 176 41, 6 176 42, 6 177 41, 6 177 42, 6 178 41, 6 178 42, 281111MW, 281111MG, 281111MB, 281111DS, 281111CH, 281111DB, 281111BA, 281111BB, 281114MW, 281114MG, 281114MB, 281114DS, 281114CH, 281114DB, 281114BA, 281114BB

**Additional information**

13A 250V~, flush type, IP20, Class I, rewirable, with 1 gang switched socket outlets comply with type G (configuration of BS 1363-2), with shutters, with single pole switch, with plastic cover plate, with or without metal frame, with or without indicator lamp, details refer to annex

Annex:

6 176 41: with white front cover and white cover plate, without metal frame;  
6 176 42: with white front cover and white cover plate, with indicator lamp, without metal frame;  
6 177 41: with dark front cover and dark cover plate, without metal frame;  
6 177 42: with dark front cover and dark cover plate, with indicator lamp, without metal frame;  
6 178 41: with ivory front cover and ivory cover plate, without metal frame;  
6 178 42: with ivory front cover and ivory cover plate, with indicator lamp, without metal frame;

281111MW: with dark front cover and matt white cover plate, with metal frame;  
281111MG: with dark front cover and matt grey cover plate, with metal frame;  
281111MB: with dark front cover and matt black cover plate, with metal frame;  
281111DS: with dark front cover and dark silver cover plate, with metal frame;  
281111CH: with dark front cover and champagne cover plate, with metal frame;  
281111DB: with dark front cover and dark bronze cover plate, with metal frame;  
281111BA: with dark front cover and brushed aluminium cover plate, with metal frame;  
281111BB: with dark front cover and brushed black cover plate, with metal frame;

281114MW: with dark front cover and matt white cover plate, with metal frame, with indicator lamp;  
281114MG: with dark front cover and matt grey cover plate, with metal frame, with indicator lamp;  
281114MB: with dark front cover and matt black cover plate, with metal frame, with indicator lamp;  
281114DS: with dark front cover and dark silver cover plate, with metal frame, with indicator lamp;  
281114CH: with dark front cover and champagne cover plate, with metal frame, with indicator lamp;  
281114DB: with dark front cover and dark bronze cover plate, with metal frame, with indicator lamp;  
281114BA: with dark front cover and brushed aluminium cover plate, with metal frame, with indicator lamp;  
281114BB: with dark front cover and brushed black cover plate, with metal frame, with indicator lamp.

Date: 09 March, 2021

Signature: 