IEC SYSTEM FOR MUTUAL RECOGNITION OF TEST CERTIFICATES FOR ELECTRICAL EQUIPMENT (IECEE) CB SCHEME

CB TEST CERTIFICATE

Product

Switches

Name and address of the applicant

LEGRAND Magyarország Villamossági Rendszerek ZRt.

Ipartelepi út 14. 6600 Szentes

Hungary

Name and address of the manufacturer

LEGRAND Magyarország Villamossági Rendszerek ZRt.

Ipartelepi út 14. 6600 Szentes

Hungary

Name and address of the factory

Note: When more than one factory, please report on page 2

See additional page(s) for the listing of 2 factories

Ratings and principal characteristics

For new type (Niloé) and new design (Niloé step): 250 V~, 6 A, 6 AX, 10 A, 10 AX, 16 AX, IP20, IP44

Trademark / Brand (if any)

legrand

Customer's Testing Facility (CTF) Stage used

Model / Type Ref.

A027737, A027738, A027769, A027770, A027771, A027765, A027766, A027767, A027768, A027777, A027778, A027779, RB6, BI10V1, KCA1, PE10V1, A030816, A030931, A027772, A030822 For detailed type differences and designation see add. pages this CB Test Certificate.

For available accessories see CB Test Report.

Additional information (if necessary may also be reported on page 2)

See additional page(s) for further Additional information. This CB Test Certificate is modification No.3 for HU-004323, dated 2023-03-16 and it is issued due to additional new types for "Niloé" and new design: "Niloé step". In this CB Test Certificate only the new additional types and their ratings have been listed.

A sample of the product was tested and found to be in conformity with

IEC 60669-1:2017

As shown in the Test Report Ref. No. which forms part of this Certificate

HU215VBB 004

This CB Test Certificate is issued by the National Certification Body



TÜV Rheinland InterCert Kft., MEEI Division H-1143 Budapest, Gizella út 51-57., Hungary Web: www.tuv.com

2025-03-04 Date:

Signature:

Tötös Tamás László





Page 2 of 10

Additional information:

Type differences and designation:

Type reference: A030816 (with "Niloé" design)

Designation: Flush type push-button, pattern no 6

Type of term.: screwless Rated current: 10 A

ReI. no. Color Degree of protection NP2316WH white IP20 / IP44 NP2316MG mid. grey IP20 / IP44 NP2316BK black

Type reference: A030931 (with "Niloé" design)

Designation: Flush type double push-button, pattern no 6+6

Type of term.: screwless Rated current: 10 AX

Ref. no. Color Degree of protection NP2326WH white IP20 / IP44 NP2326MG mid. grey IP20 / IP44 NP2326BK black

Type reference: A027737 (with "Niloé step" design) Designation: Roller blind switch, pattern no 4

Type of term.: screw Rated current: 10 AX

Degree of protection IP20 / IP44 Ref. no. Color

8 631 44B white 8 633 44B aluminium IP20 / IP44 mid. grey 8 634 44B IP20 / IP44 black IP20 / IP44 8 635 44B IP20 / IP44 8 640 32B

Type reference: A027738 (with "Niloé step" design) Designation: Roller blind push-button, pattern no 4 Type of term.: screw

Rated current: 6 A

Degree of protection Ref. no. Color

8 631 43B white IP20 / IP44 aluminium IP20 / IP44 8 633 43B mid. grey IP20 / IP44 8 634 43B 8 635 43B black IP20 / IP44 8 640 30B IP20 / IP44



TÜVRheinland®



Page 3 of 10

Additional information:

Type reference: A027769 (with "Niloé step" design)

Designation: Two-way switch, pattern no 6

Type of term.: screwless Rated current: 10 AX

Degree of protection IP20 / IP44 Ref. no. Color

3 982 00B white 3 982 20B white IP20 / IP44 3 982 21B aluminium IP20 / IP44 3 982 22B black IP20 / IP44

Type reference: A027769 (with "Niloé step" design)

Designation: 5x multipack two-way switch, pattern no 6

Type of term.: screwless Rated current: 10 AX

Degree of protection Color Ref. no.

3 983 00B white IP20 / IP44

Type reference: A027769 (with "Niloé step" design)

Designation: 3x multipack two-way switch, pattern no 6

Type of term.: screwless Rated current: 10 AX

Degree of protection Color Ref. no.

IP20 / IP44 3 983 02B aluminium 3 983 04B black IP20 / IP44

Type reference: A027769 (with "Niloé step" design)

Two-way switch, pattern no 6

Designation: Two-way so Type of term.: screwless Rated current: 10 AX

Degree of protection Ref. no. Color

white IP20 / IP44 aluminium IP20 / IP44 8 631 06B 8 633 06B 8 634 06B mid. grey IP20 / IP44 8 635 06B black IP20 / IP44 IP20 / IP44 8 640 06B



TÜVRheinland®



Page 4 of 10

Additional information:

Type reference: A027769 (with "Niloé step" design) Designation: Two-way switch x 50, pattern no 6

Type of term.: screwless Rated current: 10 AX

Ref. no. Color Degree of protection 8 641 90B white IP20 / IP44

Type reference: A027770 (with "Niloé step" design)

Designation: Illuminated two-way switch, pattern no 6 Type of term.: screwless, led lamp: CF00078 Rated current: 10 AX

Ref. no.	Color	Degree of protection
3 982 23B	white	IP20 / IP44
3 982 24B	aluminium	IP20 / IP44
3 982 25B	black	IP20 / IP44
8 631 16B	white	IP20 / IP44
8 633 16B	aluminium	IP20 / IP44
8 634 16B	mid. grey	IP20 / IP44
8 635 16B	black	IP20 / IP44

Type reference: A027771 (with "Niloé step" design) Designation: 2-gang two-way switch, pattern no 6+6
Type of term.: screwless
Rated current: 10 AX

Ref. no.	Color	Degree	of protection
3 982 02B	white	IP20 /	IP44
3 982 26B	white	IP20 /	IP44
3 982 27B	aluminium	IP20 /	IP44
3 982 28B	black	IP20 /	IP44
8 631 08B	white	IP20 /	IP44
8 633 08B	aluminium	IP20 /	IP44
8 634 08B	mid. grey	IP20 /	IP44
8 635 08B	black	IP20 /	IP44
8 640 08B	-	IP20 /	IP44



TÜVRheinland®





Page 5 of 10

Additional information:

Type reference: A027765 (with "Niloé step" design)

Designation: One-way switch, pattern no 1

Type of term.: screwless Rated current: 10 AX

Degree of p IP20 / IP44 Ref. no. Color Degree of protection 8 631 01B white 8 633 01B aluminium IP20 / IP44

8 634 01B mid. grey IP20 / IP44 8 635 01B black IP20 / IP44 8 640 01B IP20 / IP44

Type reference: A027766 (with "Niloé step" design)

Designation: Illuminated one-way switch, pattern no 1
Type of term.: screwless, led lamp: CF00078
Rated current: 10 AX

Color Degree of protection Ref. no.

8 631 11B white IP20 / IP44 8 633 11B aluminium IP20 / IP44 mid. grey 8 634 11B IP20 / IP44 IP20 / IP44 8 635 11B black

Type reference: A027767 (with "Niloé step" design) Designation: 2-gang one-way switch, pattern no 5 Type of term.: screwless

Rated current: 10 AX

Color Degree of protection white TP20 / TP44 Ref. no. white 8 631 05B

IP20 / IP44 IP20 / IP44 aluminium 8 633 05B mid. grey IP20 / IP44 8 634 05B 8 635 05B black IP20 / IP44 8 640 05B IP20 / IP44

Type reference: A027768 (with "Niloé step" design)

Designation: Illuminated 2-gang one-way switch, pattern no 5

Type of term.: screwless, led lamp: CF00078

Rated current: 10 AX

Ref. no. Color Degree of protection

8 631 15B IP20 / IP44 white 8 633 15B aluminium IP20 / IP44 8 634 15B mid. grey IP20 / IP44 8 635 15B black IP20 / IP44



TÜVRheinland®



Page 6 of 10

Additional information:

Type reference: A027777 (with "Niloé step" design) Designation: 2-gang 1-way push-button, pattern no 5

Type of term.: screwless

Rated current: 6 A

Degree of p IP20 / IP44 Ref. no. Color Degree of protection 8 631 12B white

8 633 12B aluminium IP20 / IP44 8 634 12B mid. grey IP20 / IP44 8 635 12B black IP20 / IP44

Type reference: A027778 (with "Niloé step" design)

Designation: Push-button, pattern no 1

Type of term.: screwless

Rated current: 6 A

Ref. no. Color Degree of protection 8 631 09B white IP20 / IP44

8 633 09B aluminium IP20 / IP44 8 634 09B mid. grey IP20 / IP44 8 635 09B black IP20 / IP44

Type reference: A027779 (with "Niloé step" design)

Designation: Illuminated push-button + picto bell, pattern no 1

Type of term.: screwless, led lamp: CF00078 Rated current: 6 A

Degree of protection Ref. no. Color

8 631 10B white IP20 / IP44 8 633 10B aluminium IP20 / IP44 mid. grey 8 634 10B IP20 / IP44 IP20 / IP44 8 635 10B black

Type reference: A027779 (with "Niloé step" design) Designation: Illuminated push-button, pattern no 1 Type of term.: screwless, led lamp: CF00078

Rated current: 6 A

Color Degree of protection white TP20 / TP44 Ref. no.

8 631 13B white IP20 / IP44 aluminium IP20 / IP44 8 633 13B mid. grey IP20 / IP44 8 634 13B black 8 635 13B



TÜVRheinland®



Page 7 of 10

Additional information:

Type reference: BI10V1 (with "Niloé step" design)

Designation: 2-pole switch, pattern no 2

Type of term.: screw Rated current: 10 AX

Ref. no. Color Degree of protection

Degree of p IP20 / IP44 8 631 02B white 8 633 02B aluminium IP20 / IP44 8 635 02B black IP20 / IP44 8 640 28B IP20 / IP44

Type reference: KCA1 (with "Niloé step" design)

Designation: Mechanical keycard switch (hotel), pattern no 1

Type of term.: screwless

Rated current: 6 A

Ref. no. Color Degree of protection 8 631 46B white IP20 / IP44

8 633 46B aluminium IP20 / IP44 8 634 46B mid. grey IP20 / IP44 black 8 635 46B IP20 / IP44 IP20 / IP44 8 640 15B

Type reference: PE10V1 (with "Niloé step" design)

Designation: Intermediate switch, pattern no 7 Type of term.: screw

Rated current: 6 A

8 640 07B

Color Degree of protection white IP20 / JP44 Ref. no. white IP20 / IP44 aluminium IP20 / IP44 black IP20 / IP44 white 3 982 29B 3 982 30B black IP2U / IP44 3 982 31B 8 631 07B white 8 633 07B aluminium IP20 / IP44 8 634 07B mid. grey IP20 / IP44 black 8 635 07B IP20 / IP44 IP20 / IP44



TÜVRheinland®



Page 8 of 10

Additional information:

Type reference: A030816 (with "Niloé step" design) Designation: Changeover push-button, pattern no 6

Type of term.: screwless

Rated current: 10 A

Ref. no. Color Degree of p 3 982 32B white IP20 / IP44 Degree of protection

3 982 33B aluminium IP20 / IP44 3 982 34B black IP20 / IP44 8 640 11B IP20 / IP44

Type reference: A030931 (with "Niloé step" design)

Designation: 2-gang changeover push-button, pattern no 6+6

Type of term.: screwless

Rated current: 10 A

Ref. no. Color Degree of protection

8 640 12B IP20 / IP44

Type reference: BI10V1 (with "Niloé step" design) Designation: 2-pole indicator switch, pattern no 2

Type of term.: screw, led lamp: 6 650 91

Rated current: 10 AX

Color Degree of protection Ref. no.

IP20 / IP44 8 640 29B

Type reference: A027772 (with "Niloé step" design)

Designation: Illuminated 2-gang two-way switch, pattern no 6+6 Type of term.: screwless, led lamp: CF00078 Rated current: 10 AX

Color Degree of protection white IP20 / IP44 Ref. no.

white IP20 / IP44 aluminium IP20 / IP44 8 631 18B 8 633 18B IP20 / IP44 mid. grey 8 634 18B 8 635 18B black IP20 / IP44



TÜVRheinland®







Page 9 of 10

Additional information:

Type reference: RB6 (with "Niloé step" design)

Designation: Roller blind switch 3 pos, pattern no 4

Type of term.: screwless

Rated current: 6 AX

Ref. no. Color Degree of protection 3 982 44B white IP20 / IP44

3 982 45B aluminium IP20 / IP44 3 982 46B black IP20 / IP44 8 640 31B black IP20 / IP44

Type reference: A030822 (with "Niloé step" design)

Designation: Two-way switch, pattern no 6

Type of term.: screwless Rated current: 16 AX

Ref. no. Color Degree of protection 8 640 16B - IP20 / IP44





Ref. Certif. No.

HU-004323-A1/M3

Page 10 of 10

Factories:

- Legrand Egypt, EMB Electrical Industrial S.A.E.

 1. Plot 18, 2nd Industrial zone 32897 Sadat City, Menoufia Egypt
- LEGRAND Magyarország Villamossági Rendszerek ZRt. 2. Ipartelepi út 14. 6600 Szentes Hungary



Date: 2025-03-04 Signature: as on page 1